

VS-PC-2XGOF-50-SCRJ/SCDU-1

Order No.: 1654400



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1654400>

Assembled fiber optic cable, break-out cable, glass fiber multi-mode 50/125 µm, SCRJ/IP20 on SC-duplex/IP20, for installation inside control cabinets, length: 1 m

Commercial data

EAN	4017918970680
Pack	1 pcs.
Customs tariff	85447000
Weight/Piece	0.07415 KG
Catalog page information	Page 216 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
11/09/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

Mechanical characteristics

Connection profile	SCRJ according to DIN EN 50377-6-1
Fiber type	Multimode glass fibers
Fiber	50/125 µm
Ferrule diameter	2.50 mm


Number of fibers	2
External cable diameter	Twin conductor (2.8 x 5.7 mm)
Type of cable	Break-out cable
Smallest bending radius, fixed installation	60 mm
Smallest bending radius, movable installation	60 mm
Length of cable	1 m
Ambient temperature (operation)	-5 °C ... 70 °C

Material data



Housing material	PBT
Outer sheath, material	LSZH
External sheath, color	orange
Ferrule material	Zirconia ceramics
Ferrule holder color	White
Degree of protection	IP20

Diagrams/Drawings


Dimensioned drawing



SCRJ plug connector IP20



SC duplex connector IP20



Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;