

PIEZO INDICATOR (Wire Type)

Internal Circuitry Type

Shape


KPE-251
KPE-253



RoHS Compliant Available (eg.KPEG251,KPEG253)

Model Number	KPE-251	KPE-253
Rated Frequency (Hz)	3,500 ± 500	
Operating Voltage Range (VDC)	4 ~ 28	
Current Consumption (mA)	Max. 5@12VDC	Max. 6@12VDC
Sound Pressure Level (dB)	Min.82dB@30cm@12VDC	Min.87dB@30cm@12VDC
Tone	Fast Pulse (3.0Hz±20%)@12VDC	Slow Pulse (1.2Hz±20%)@12VDC
Operating Temperature (°C)	-30 ~ +85	
Storage Temperature (°C)	-40 ~ +95	
Weight (Gram)	10.1	10.2
Material	ABS UL-94 1/16" HB High Heat (Black)	


Dimension



Tol : ±0.5 Unit : mm

Characteristic

KPE-251



KPE-253

