






Dimensions:mm (In.)



Electrical Specifications:

- Rating: 50mA/12VDC
- Contact resistance: 100mΩ max.
- Insulation resistance: 100MΩ min. @ 500VDC
- Dielectric strength: 250VAC for 1 minute
- Life: 500,000 cycles

Mechanical Specifications:

- Type: SPST
- Operating force: 160±50gf
- Stroke: .35mm +.2mm -.1mm
- Operating temperature: -25°~+70°C

Soldering Process:

- Wave soldering temperature: 260°C(500°F) max. for 5 seconds with 1.6mm thick PCB
- Hand soldering temperature: 320°C(608°F) max. for using a 30W soldering iron

Material:

- Button color: brown

Tactile Switch (Thru-Hole)
101-0621



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-0621](#)