

HC-B 48-TFL/PG36S

Order No.: 1772146

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1772146>

Sleeve housing, for single locking latch, height 96 mm, with screw connection, 1x Pg36, lateral cable entry

Commercial data

EAN	4017918036812
Pack	1 pcs.
Customs tariff	85389099
Weight/Piece	0.8123 KG
Catalog page information	Page 506 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
03/01/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data

Note	For contact inserts HC-B48, DD216, M
Design	B48
Height	96 mm
Width	89 mm

Length	131.5 mm
Housing type	Sleeve housings
Locking type	for single locking latch
Type of the screw connection	1x Pg36
Pg screw connection	With
Wrench size, union nut	47 mm
Cable exit	Lateral
External cable diameter	24 mm ... 33 mm
Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 125 °C
Housing material	Aluminum, die-cast
Housing surface material	Powder-coated, gray
Cable gland material	Nickel-plated brass
Cable seal material	NBR

Certificates / Approvals




Certification

GOST

Diagrams/Drawings

Dimensioned drawing



Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;