


PART NAME	PLASTICASE	PART No.	PC-11406 TO PC-11416
-----------	------------	----------	----------------------



NOTE: ALL DIMENSIONS HAVE ±0.015 TOLERANCE
UNLESS OTHERWISE SPECIFIED

MATERIAL: IMPACT RESISTANT POLYSTYRENE (UL94-HB)
FINISH: DOUBLE-TEXTURED PC BONE GRAY

PC-11406 & PC-11408 SUPPLIED WITH TWO (2) #6 × 1.750" LG. SCREWS & FOUR (4) RUBBER FEET FOR ASSEMBLY
PC-11410 & PC-11412 SUPPLIED WITH TWO (2) #6 × 2.500" LG. SCREWS & FOUR (4) RUBBER FEET FOR ASSEMBLY.
PC-11414 & PC-11416 SUPPLIED WITH TWO (2) #6 × 3.250" LG. SCREWS & FOUR (4) RUBBER FEET FOR ASSEMBLY.

NOTE: MOUNTING BOSSSES USE EITHER M2.5 METRIC OR #4 STD. SHEET METAL SCREWS × 0.250" LG. (NOT SUPPLIED).

* - NUT RETAINERS NOT INCLUDED IN THE BASES OF UNITS MARKED WITH ASTERICKS

PART No.	STYLE	A	B	C	D	E	F	G	H	J	K	L	M	N	P
* PC-11406	A	2.520	6.120	2.270	1.970	---	5.000	5.280	5.770	2.180	0.880	2.310	5.750	2.180	5.650
PC-11408	A	2.520	8.100	2.270	1.970	---	6.980	7.260	7.750	3.120	0.930	2.310	7.750	2.180	7.650
* PC-11410	B	3.300	6.120	3.050	2.750	2.040	5.000	5.280	5.770	2.180	0.880	3.080	5.750	2.930	5.650
PC-11412	B	3.300	8.100	3.050	2.750	2.040	6.980	7.260	7.750	3.120	0.930	3.080	7.750	2.930	7.650
* PC-11414	B	4.040	6.120	3.790	3.490	2.780	5.000	5.280	5.770	2.180	0.880	3.830	5.750	3.680	5.650
PC-11416	B	4.040	8.100	3.790	3.490	2.780	6.980	7.260	7.750	3.120	0.930	3.830	7.750	3.680	7.650