

Support > VIERA Televisions > VIERA Plasma HDTVs > TC-L37X2

37" Class Viera® X2 Series 720p LCD

FIND ANOTHER MODEL

Model number: TC-L37X2

[Print this](#) | [Share this](#)

Product no longer available for purchase.

37" Class Viera® X2 Series 720p LCD
(37.0" Diagonal)

- iPod® Dock
- VIERA Image Viewer™
- VIERA Link™
- ENERGY STAR Qualified

Online Order Assistance

- Track your order
- Print your invoice
- Read our shipping FAQs
- Register your product

Accessories

- Find accessories for your product

Contact Us

- Live Chat
- Phone
- Email
- Mail
- International Support

Operating Manuals	Help & Tutorials	FAQs	Tech Specifications	Warranty & Care Plans	Accessories	Drivers & Downloads
Model Type				LCD		
Series				X2		
Model Year				2010		
VIDEO						
Screen Size				37" Class (37.0" diagonal)		
Viewing Angle				178°		
Aspect Ratio				16:9		
Native Resolution (Number of Pixels)				1,049,088 (1,366 x 768)		
HDTV Display Capability (1080p, 1080i, 720p)				720p		
EDTV Display Capability (480p)				Yes		
Aspect Control				480i/p: Full, Just, 4:3, Zoom 1080i/p: Full, H-Fill, Just, 4:3, Zoom		
Panel				IPS (WXGA)		
Filter				Fine Black Panel		
Backlight				EEFL		
Progressive Scan				Yes		
24p Playback(2:3)				Yes		
Intelligent Scene Controller				Yes		
Motion Focus Technology				No		
Contrast (Dynamic)				20,000:1		
120 Hz				No		
24p Smooth Film				No		
AUDIO						
Speakers				Full-range x 2 (L, R)		
Number of Speakers				2		
Audio Output				20 W (10% THD)		
Surround Sound				Yes		
INPUTS & JACKS						
Integrated ATSC Tuner				Yes		
VIERA Image Viewer™				Y (JPEG playback)		
HDMI Input				3 (1 side)		
Analog Audio Input (for HDMI)				Yes		
Composite Video Input				2 (1 side)		
Audio Input (for Video)				2 (1 side)		
PC Input				1		
Component Video Inputs (Y, PB, PR)				1		
Audio Input (for Component Video)				1		
Digital Audio Output				1 (5.1 ch)		
HDMI Input-Support Feature				Audio Return Channel (Input 1)		
CONVENIENCE						
VIERA Link™				Yes		
Universal Dock for iPod				Yes		
VIERA® Tools				Yes		
Game Mode				Yes		
Clean Touch Bezel				Yes		
Built-In Closed Caption Decoder				Yes		
Off - Timers				Yes		
Trilingual Menu				English/Spanish/French		
GENERAL						
Power Supply				AC 110 - 127 V, 60 Hz		
Rated Power Consumption				153 W		
Standby Power Consumption				0.3 W		
On Mode Average Power Consumption				75.0 W		
Energy Star				Yes		
Receiving System				ATSC/QAM/NTSC		
Operating Temperature				32°F - 104°F (0°C - 40°C)		
Safety Standard				UL6500/C-UL		
Swivel Angle				No		
Tilt Angle				No		
VESA Compatible				Yes		
Optional Wall-mounting Bracket				TYWK3L2RW		
SPECIFICATIONS				.		
Dimensions (H x W x D) with Stand				24.4" x 36.0" x 11.3"		
Dimensions (H x W x D) without Stand				22.8" x 36.0" x 3.5"		
Weight (lbs.) w/Stand				34.2 lbs.		
Weight (lbs.) without Stand				29.8 lbs.		
Carton Dimensions				26.1" x 49.4" x 7.5"		
Gross Weight [lbs (kg)]				39.7 lbs. (18.0 kg)		
Weight				39.7 lbs		