


Ninigi

D A T A S H E E T

ZL262-DG SERIES FEMALE HEADER PITCH 2.54 MM (0.100")




Specification:

- 1) To +105° Current Rate: 3 A
- 2) Dielectric Withstanding Voltage: 500 VAC
- 3) Insulation Resistance: 5000 MW
- 4) Temperature: -55°C ~ 105°C
- 5) Insulator: Thermoplastic (UL94V-0)
- 6) Contact: Copper Alloy
- 7) Contact Plated: Gold Flash

Series No.	No. of Contact (N)
------------	--------------------

ZL262-10DG	2 x 5
ZL262-16DG	2 x 8
ZL262-20DG	2 x 10
ZL262-26DG	2 x 13
ZL262-32DG	2 x 16
ZL262-40DG	2 x 20
ZL262-50DG	2 x 25
ZL262-80DG	2 x 40

Pitch: 2.54 mm



$$A = 2.54 * (N-1)$$

$$B = 2.54 * N$$

All dimensions in mm.