




NOTE: 1) ALL DIMS. ARE IN MILLIETER (MM)  
2) BRASS PINS WITH NICKEL PLATED

#### TEST SPECIFICATION

| EACH PLUG IS 100% TEST TO THE FOLLOWING |             |
|-----------------------------------------|-------------|
| EARTH CONTINUITY                        |             |
| POLARITY                                |             |
| INSULATION RESISTANCE                   | 500V d.c.   |
| ELECTRICAL STRENGTH                     | 2.0KV, 50Hz |

| PART NO. | L ±                     | APPROVED |
|----------|-------------------------|----------|
|          |                         |          |
| COLOR    | LENGTH TOTAL TOLERANCE: |          |
|          | 500 ≥ L ± 20            |          |
|          | 500 < L < 1000 ± 30     |          |
|          | L ≥ 1000 ± 50           |          |

#### PRODUCT SPECIFICATION

PLUG NO: SP-023 EUROPEAN TWO-POLE PLUG WITH DUAL  
EARTHING CONTACTS FOR CLASS I APPLIANCES

RATING: 16A 250V

STANDARD: CEE7 NEM-EN50075

APPROVAL:         

MARKING:

1-SHONG

16A 250V

CE5300

△ JACKET COLOR: BLACK

MARKING:

1-SHONG <CEE> KEMA-KOOR 405+03+10 <CEE> △ CEEB 809

①②③④ NF-USE 1105 IEMEDU H05W-F 30 0.75mm<sup>2</sup>

34SL/75 088228 IEC 227

UNLESS OTHERWISE  
SPECIFIED TOLERANCE

|     |      |
|-----|------|
| 0.  | ±1.0 |
| .0  | ±0.5 |
| .00 | ±0.3 |

SCALE: AS SHOWN UNIT: mm

DRAWN: JOE 05/19/05

CHECKED: *pearl* 05/20/05

APPROVED: *Joseph* 05/20/05

ASSMANN  
Electronics

DRAWN NAME:  
AK535-1.8

PRODUCT NO.  
FILE NAME: B11E0703A0013(N)

C ECN-0505116(Emily)△(7,F)(9,E)

B ECN-0505049(Emily)△(1,B)

A ECN-0504100(Emily)

REV. DESCRIPTION

05/19/05

04/27/05

04/12/05

DATE

SIZE

REV. C

A4