

OMB5200 Series

432x348x132.6

(17"x 13.7"x 5.22")



OA300ST Series

432x203x44.5mm

(17"x 8"x 1.75")

FRONT



BACK

FRONT



BACK

Lighted rocker switch

Resettable circuit breaker.

Unit slides in to any standard 19" rack.

Tray features 3 high performance sealed ball bearing fans.

Black electro deposit finish for long life

Unit slides in to any standard 19" rack.

Tray features 2 high performance sealed ball bearing fans.

Power cord configured for standard 115 VAC or 230 VAC connection

Part Number	OMB5200-120	OMB5200-230	OA300ST-120	OA300ST-230
No. of Fans	2	2	3	3
Bearing System	Dual Ball Bearing	Dual Ball Bearing	Dual Ball Bearing	Dual Ball Bearing
Nominal Voltage (60Hz)	115 VAC	230 VAC	115 VAC	230 VAC
Input Power	70 Watts	70 Watts	45 Watts	45 Watts
Rated Speed (RPM)	3500	3500	3000	3000
Airflow (CFM)	340	340	310	310
Noise Level (dB)	57	57	53	53
Life Expectancy	60,000 hrs (25C)	60,000 hrs (25C)	60,000 hrs (25C)	60,000 hrs (25C)
Connection	1.8M Power Cord	1.8M Power Cord	2M Modular Power Cord	2M Modular Power Cord