


ASSY. NO.	LED COLOR (DIFFUSED)	
	TOP POSITION	BOTTOM POSITION
571-0111-100F	RED	RED
571-0102-100F	BLANK	GREEN
571-0112-100F	RED	GREEN
571-0113-100F	RED	YELLOW
571-0120-100F	GREEN	BLANK
571-0122-100F	GREEN	GREEN
571-0123-100F	GREEN	YELLOW
571-0132-100F	YELLOW	GREEN
571-0133-100F	YELLOW	YELLOW

NOTES:



- LED LEAD DIMENSIONS ARE MEASURED AT HOUSING EXIT.
- PIN NUMBERS FOR REFERENCE ONLY. DESIGNATION NON-EXISTENT ON PARTS.
- PART NO. 571-01XX-100 WITH PINS (SEE CHART).



OPERATING CHARACTERISTICS AT 25°C AMBIENT


CHARACTERISTICS	COLOR	MIN	TYP	MAX	UNITS	TEST CONDITIONS
LUMINOUS INTENSITY	RED	8	15		mcd	I _F = 10 mA
	YELLOW	5	8			
	GREEN	5	10			
FORWARD VOLTAGE	RED	2.0	2.0	2.5	V	I _F = 20 mA
	YELLOW		2.1	2.5		
	GREEN		2.2	2.5		
DOMINANT WAVELENGTH	RED		625		nm	
	YELLOW		588			
	GREEN		568			
PEAK EMISSION WAVELENGTH	RED		627		nm	
	YELLOW		590			
	GREEN		565			
VIEWING ANGLE 2 θ 1/2	RED		70		Degree	
	YELLOW		70			
	GREEN		70			
CAPACITANCE	RED		15		pF	V _F = 0 V, f = 1 MHz
	YELLOW		20			
	GREEN		15			

ABSOLUTE MAXIMUM RATING AT 25°C AMBIENT	RED	YELLOW	GREEN	UNITS
POWER DISSIPATION	105	105	105	mW
FORWARD CURRENT	30	30	25	mA
DERATING LINEAR FROM 25 °C		.40	.33	mA/°C
REVERSE VOLTAGE		5		V
LEAD SOLDERING TEMPERATURE, 5 SEC., 1/16" FROM BODY		260		°C
OPERATING TEMPERATURE		-40 TO +85		°C
STORAGE TEMPERATURE		-40 TO +85		°C



RECOMMENDED P.C.B. HOLE PATTERN

Rohs Compliant 571-01XX-100F
Part Numbers with the "F" suffix ending are RoHS Compliant.
Example: 571-0120-100F
Packaging is marked with "RoHS Compliant" label or equivalent markings.
Parts can be wave soldered, dip soldered or hand soldered using typical lead-free soldering process with max 260°C temp. for 5 sec.



THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT.

SCALE: 4.000	DRAWING NUMBER		REV
ALL DIM'S IN: INCHES (MM)	C-17537		A
TOLERANCES: UNLESS OTHERWISE SPECIFIED			
FRACTIONS: $\pm 1/64$	TITLE		1.8mm LED BI-LEVEL CBI
DECIMALS (.XX): $\pm .01$	MATERIAL		RoHS COMPLIANT
DECIMALS (.XXX): $\pm .005$			
ANGLES: $\pm 1^\circ$			
FINISH:			
FSCM	83330	SHEET 1 OF 1	FAMILY TABLE:
			1501 ROUTE 34 SOUTH FARMINGDALE, NJ 07727