

INTERFACES CONNECTOR-TO-WIRE

Ribbon Cable Module 35 or 32mm DIN Rail

Compact Ribbon Connector Modules provide an interface between multiwire flat cables outfitted with IDC connectors and discrete wires. Up to 64 conductors can be terminated saving time and eliminating wiring mistakes.

No special wiring or tools are required. Ribbon Cable interface modules are typically used in communications, data processing, process control and other industrial applications.


FBK Ribbon Cable Modules are supplied with short strain relief ejector latches (long ejector latches are available), screw-cage clamp terminal blocks and component solder pads for easy insertion of circuit building components. All terminal blocks are individually marked to correspond to the numbers on the header pins.

- Screw-Cage Clamp Connections
- Up to 64 Poles
- 4 to 5 Component Solder Pads Per Line
- .9mm (.035 in.) Component Mtg. Holes
- DIN Rail Mount, Panel Mount Available

Ordering Information **No. of Poles**


Ribbon Cable Module with Short Ejector Latches^a

Type	Cat. No.	Module Length (L) mm (in.)	Std. Pk.
FBK10	5720.2	47 (1.85)	1
FBK14	5721.2	47 (1.85)	1
FBK16	5722.2	69 (2.72)	1
FBK20	5723.2	69 (2.72)	1
FBK26	5724.2	80 (3.15)	1
FBK34	5725.2	103 (4.06)	1
FBK40	5726.2	114 (4.49)	1
FBK50	5727.2	148 (5.83)	1
FBK60	5728.2	170 (6.68)	1
FBK64	5729.2	170 (6.68)	1



FBK Ribbon Cable with Short Ejector Latches

Wire Range	Current	Voltage
0.5-4mm ² 22-12 AWG	3A	250V AC



^aTo order long ejector latches, specify Cat. No. with /L suffix.
Example: Cat. No. 5727.2/L.