



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	WEIGHT
 WG18FRTB**	4.55 LBS/EACH (2063.8 g/EACH)





NOTE:


- PANDUIT PART NUMBER WG18FRTB** INCLUDES:
 - ONE (1) WYR-GRID 18" WIDTH FIBERRUNNER TRAPEZE BRACKET ASSEMBLY FOR 4X4 AND 6X4
 - TWO (2) WYR-GRID FIBERRUNNER TRAPEZE UPRIGHT SUPPORT BRACKET ASSEMBLIES
 - TWO (2) 1/4-20 X 3/4 HEX HEAD CAP SCREWS
 - FOUR (4) 1/4 -20 HELICAL SPRING LOCKWASHERS
 - TWO (2) 1/4-20 SAE FLAT WASHER
 - TWO (2) WYR-GRID INTEGRAL BRACKET LOWER CLIP ASSEMBLIES
 - TWO (2) 1/4-20 X 1-1/8 HEX HEAD CAP SCREWS
- DIMENSIONS IN PARENTHESES ARE METRIC.
- PROVIDES ABILITY TO MOUNT FIBERRUNNER 6.6" TO 9.9" ABOVE WYR-GRID.
- SEE CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE PART FINISH AND/OR PACKAGE QUANTITY.



ADJUSTMENT
RANGE
12.2 MAX
(309.9)
8.9 MIN
[226.1]



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
4	09-06-13	SSP	KMC	RN	I. REVISED INTEFRAL TO INTEGRAL ON NOTE 1.F	10D166AG-DC
3	03-27-13	SSP	DWR	RN	H. REVISED THE ADJUSTMENT RANGE TOLERANCES G. ADDED '**' SUFFIX TO PANDUIT PART NUMBER F. ADDED NOTE #4 TO GENERAL NOTES E. REMOVED PRIOR NOTE(S)	10D166AG-DC

TITLE WYR-GRID 18" WIDTH FIBERRUNNER TRAPEZE BRACKET FOR 4X4 AND 6X4 (WG18FRTB**)						
CUSTOMER DRAWING						
ITEM REVISION NAME						
10D166AG/03.PRT						
DATASET FILE NAME						
10D166AG-DC/03E WG18FRTB**.PRT						
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]						
.X ± .XX ± .05 [1.3]						
.XXX ± ANGLES ±						
						
THIRD ANGLE PROJECTION						
DRAWN BY						
JAHA						
DATE						
06-11-10						
CHK						
EB						
SCALE						
NONE						
MATERIAL:						
STEEL						
DRAWING NUMBER:						
10D166AG-DC						
SHT 1 OF 1						
SIZE						
A						