

KLIPPON K4 EX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



For many years, the name Klippon has stood for competence and quality in enclosures and customer-specific, connection-ready applications. Customer satisfaction is our number one priority. That is why we have updated and modernized our line of aluminium housings. These are improved products for all application requirements.

General ordering data

Order No.	9526910000
Part designation	KLIPPON K4 EX
Version	Enclosures, 82 mm, 72 mm, 130 mm, Aluminium AISi12
GTIN (EAN)	4032248019083
Qty.	1 pc(s).

KLIPPON K4 EX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-2083
 www.weidmueller.com

Technical data

Dimensions (1)

Weight	620 g	Length	72 mm
Width	130 mm	Height	82 mm
Fixing dimension, width	98 mm		

General information

Fixing dimension, width	98 mm	Material	Aluminium AlSi12
Surface	untreated	Cover fixing	M4 torx stainless steel screws with slot
Enclosure fixing	Holes 5 mm	Integral fixing	Threaded holes M5
Material	Aluminium AlSi12	Resistance to shocks	7.00 J
Sealing material	Silicone	Surface	untreated

Cable glands top/bottom

M 12	2	M 16	2
M20	1	M25	1
M32	1	Side of enclosure	left right

cable glands, left

M 12 (3)	5	M 16 (3)	3
M 20 (3)	2	M 25 (3)	2

cable glands, right

M 12 (2)	5	M 16 (2)	3
M 20 (2)	2	M 25 (2)	2
Side of enclosure	left right		

vertical assembly

WDU 10 / ZDU 10 (2)	1x2	WDU 2,5 / ZDU 2,5 / IDU 2,5 (2)	1x5
WDU 4 / ZDU 4 (2)	1x4	WDU 6 / ZDU 6 (2)	1x3

Approvals

Approvals institutes	GOSTEX; GOSTME25; KEMAATEX; MARITREG
----------------------	---

Classifications

eClass 5.1	27-18-05-02	eClass 6.0	27-18-05-02
------------	-------------	------------	-------------