

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:


82-28-6051

Status:

Active

Description:

2.54mm Pitch Round Conductor Flat Cable - 28 AWG (7 x 36) Stranded, Topcoat, 5 Circuits, Reel 30.48m Length



Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
CSA	LR61126
UL	E61522
General	
Product Family	Cable
Series	7767
Crimp Quality Equipment	Yes
Geographic Area	Asia
Product Name	Ribbon
UPC	800755002324
Physical	
Cable Length	30.48m
Circuits (Loaded)	5
Insulation	PVC
Net Weight	468.730/g
Packaging Type	Reel
Pitch - Termination Interface	2.54mm
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	28
Wire/Cable Type	(7x36) Stranded, Topcoat
Electrical	
Current - Maximum per Contact	N/A
Voltage - Maximum	300V
Material Info	
Old Part Number	7767-05-100B
Reference - Drawing Numbers	
Sales Drawing	SD-7767-001

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

7767Series

Use With

[70400](#) C-Grid SL™ IDT Connector Assembly. [70475](#) SL™ IDT Connector Assembly. [7720](#) KK® IDT Double Cantilever Contact

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION