


PART NAME	UTILIBOX (STYLE H)	PART NO.
MATERIAL: ABS THERMOPLASTIC (FLAMMABILITY RATING OF 94-VO AT 0.070" THICKNESS AND CONTINUOUS USE TEMPERATURE OF 70° C) FINISH: BODY - OUTSIDE SURFACES ARE TEXTURED FINISH WITH TEXTURED INSERT AREA. COVER - VERTICAL OUTSIDE SURFACES ARE TEXTURED REMAINDER OF PART IS SMOOTH. COLOR: BLACK		CU-1476
 <p>LENGTH AND WIDTH DIMENSIONS ARE TAKEN FROM CLOSED END OF THE BOX. DIMENSIONS INCREASE SLIGHTLY AT OPEN END DUE TO TAPER.</p> <p>NOTE: ALL DIMENSIONS HAVE ± 0.010 TOLERANCE UNLESS OTHERWISE SPECIFIED.</p> <p>FOUR (4) #4 X 1/2 LG. SELF THREADING SCREWS WITH HOLLOW THREADS ARE SUPPLIED FOR MOUNTING COVER.</p> <p>0.056</p> <p>0.111 DIA. (AT TOP) (4) HOLES</p> <p>0.215 DIA. BOSS (4) PLACES</p> <p>0.090 DIA. X 0.250 DEEP (4) HOLES</p> <p>0.180 DIA. BOSS (4) PLACES</p> <p>0.405</p> <p>0.047 TYP.</p> <p>0.0100 TYP.</p> <p>0.100</p> <p>0.187 POLISHED BAND</p> <p>2.723</p> <p>3.974</p> <p>4.376</p> <p>1.155</p> <p>0.808</p> <p>1.155</p> <p>2.045</p> <p>3.295</p> <p>1.30° REF.</p> <p>3.125</p> <p>2.003</p> <p>2.700</p> <p>0.677</p> <p>0.797</p> <p>4.473</p> <p>4.472</p> <p>4.500</p> <p>0.405</p> <p>0.010</p> <p>0.076</p> <p>0.090 DIA. X 0.500 DEEP (4) HOLES</p> <p>0.180 DIA. BOSS (4) PLACES</p> <p>2.598</p> <p>3.848</p> <p>2.598</p> <p>3.848</p> <p>BODY</p> <p>COVER</p>		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bud Industries:](#)

[CU-1476](#)