


(1.27 mm) .050"

FFMD-20-T-02.00-01-N-R



FFMD-10-S-10.00-01

FFMD SERIES

TIGER EYE™ FLAT IDC WIRE CABLES

Mates with:

FLE*, SFMC*,

Transfer End Option

Mates with: FTS, FTSH,
EHF, SHF, ESHF

SPECIFICATIONS

For complete specifications
see www.samtec.com?FFMD

Insulator Material:

Black Glass Filled Polyester

Terminal:

Phosphor Bronze

Contact:

BeCu (-T)

Plating:

Sn over 50 μ" (1.27 μm) Ni

Wire:

30 AWG

Current Rating:

2.5 A per pin

(2 pins powered)

Operating Temp Range:

-40 °C to +105 °C

Voltage Rating:

215 VAC

304 VDC

RoHS Compliant:

Yes

RECOGNITIONS


For complete scope of
recognitions see
www.samtec.com/quality

ALSO AVAILABLE (MOQ Required)


- Other sizes
- Contact Samtec.

***Note:** Standard FFMD callout will not mate with FLE, SFMC. Must use gold plated callouts. (See drawing on web.)
When mated with a socket,
Wire 1 mates with Pin 2;
Wire 2 mates with Pin 1, etc.

Note: This Series is
non-standard, non-returnable.



FFMD = Terminal Strip



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.
Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.