

1 2 3 4 5 6 7 8

A

B

C

D

E

F

A





B

C

D

E

F



Connector type	I CONTINUOUS A(DC)	I max A(DC)	C min pF	FILTER EQUIVALENT TO
72814-204LF	10	15	3000	Tusonic 4101-066
72814-205LF				

Product number	L
72814-204LF	2.2
72814-205LF	2.7


- NOTES:
1. BODY MATERIAL: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94 V0
 2. TERMINAL MATERIAL: BRONZE
 3. TERMINAL PLATING:
Ni + GOLD ON MATING AREA
Ni + PURE Sn ON TERMINATION
 4. PACKAGING IN TUBE ACCORDING TO EUR-14-005.
 5. VOLTAGE PROOF 1000 V
 6. CURRENT CAPACITY : SEE TABLE
 7. CONTACT RESISTANCE 10 mOHM MAXI
 8. INSULATION RESISTANCE 5000 MOHM INITIAL MINI
 9. FILTER : SEE TABLE
 10. FOR MORE DETAILS REFER THE DRAWING 72846_C

14-ROHS INFORMATION:


-This product meets European Union Directives and other country regulations as described in GS-22-008.

-The housing will withstand exposure to 260°C peak temperature for 10 second in a wave solder application with a 1.6mm minimum thick circuit board. See Application notes/procedures if they are available.

-Packaging label spec: see GS-14-920.



3:1



3:1

Copyright FCI.
FCI

REV F - 2006-04-17

1 2 3 4 5 6 7 8

rev	ecr no	dr	date
D	LS06-0143	LGO	2006-09-25
E	LS07-0240	JTA	2007-09-21
F	LS08-0234	JTA	2008-12-19
G	N11-0027	A.ZH	2011-02-07
H	N11-0127	A.ZH	2011-04-22

www.fciconnect.com				surface ISO 1302	tolerance std ISO 406 ISO 1101	projection MM	size A2		Scale 4:1
				TOLERANCES UNLESS OTHERWISE SPECIFIED					
				ANGULAR	LINEAR	0.X ±0.3 0.XX ±0.1 0.XXX ±0.05	ECN N11-0127		RELEASE
				Product family		Spec ref			
FCI				RA HDR POWER ASSY		72814	Rev. H		
				FILTERED VERSION					
				SEE TABLE		CUSTOMER		sheet 1 of 1	

PDM: Rev:H

STATUS: Released

Printed: May 08, 2011