




DIM.A= 1.27 x No. of Spaces
 DIM.B= DIM.A + 5.87
 DIM.C= DIM.A + 1.80
 DIM.D= DIM.A + 3.27

*Available in 4 ~ 26 Circuits

Material:

* Insulation:

Glass Filled Polyester UL 94V-0

* Contact: Phosphor Bronze

Ordering Code:

CA32 ** V 1 3 00
 ① ② ③ ④ ⑤ ⑥

① Series No.:

② No. of Circuits: 04 to 26


③ Contacts Type:
 V= Straight Type

④ Plating option:

1= Tin over Nickel plated

⑤ Color: 3= Red

⑥ Other Option: 00= Without Latch
 OL= With Latch



RoHS Compliant

4					DATE	UNIT: mm / inch	TITLE: 1.27mm Pitch Female Top entry DIP Type Connector		 瀚荃股份有限公司 CviLux Corporation			
3				DRAWN BY: Zisley 7/20/05	TOLERANCE UNLESS OTHERWISE SPECIFIED .X ± 0.3/.012 .X' ± 1' .XX ± 0.2/.008 .X' ± .XXX ± 0.1/.004 .XX' ±	MATERIAL:						
2				ENGINEER: Zisley 7/20/05		FINISH:						
1				CHECKED BY: DAVIA 7/20/05								
SYM	NAME	DATE		APPROVED BY: Alan 7/20/05			DRAWING NO.	CA3202S2	PART NO.	CA32**V130*		
							SCALE	4 / 1	SHEET	1	OF	1