

FEATURES


Double tuning fork type contact guarantees high reliability.
1.27MM pitch Low-Profile mini type Match to 0.4 mm sq. posts.

MATERIAL

.Insulator..... 1300S NY-66(UL 94v-2)
.Contact.....Gold Plated
.Terminal.....5191 Phosphor Bronze

SPECIFICATIONS

.Current Rating: 1 amperes MAX
.Contact Resistance: 30m Ω MAX
.Insulation Resistance: 1000 megohms MAX
.Dielectric Withstanding Voltage: AC 650 volts RMS at sea level



*以下圖示塑膠公差皆為±0.15
金屬件公差為±0.05

RoHS Compliant		HSM玄茂科技股份有限公司 HSUAN MAO TECHNOLOGY CO., LTD.	
APPD. 核准	BETTY	 SCALE 比例 參考	TOLERANCE 容許公差 .0 ±0.15 .00 ± ANG. ±
DWG. 製圖	BETTY	UNIT 單位	SIZE. 紙張尺寸
DATE 制表日	2010/05/25	M M	A 4
		PAGE 張數	REV. 版次
		1 OF 1	A
		PART NAME 品名	
		1.27mm MINI JUMPER 2P H:5.5mm CLOSE COVER GOLD PLATING BLACK COLOR ROHS	
		PART NO.	
		料號 C2740-02IBGB00R	