





D

C

B

A



3D VIEW
SCALE 3:2

- 8 MOUNTING SURFACE SPECIFICATIONS:
SURFACE FINISH: 32 μ in [0.81 μ m] Ra OR LESS
FLATNESS: .005 in/in [0.13 mm/mm] MAX
7. SEE SHEET 2 FOR RECOMMENDED PANEL CUTOUTS.
6. SEE SHEET 3 FOR OTHER KEY ARRANGEMENTS.
5. MOUNTING SCREW TORQUE VALUES ARE AS FOLLOWS:
#6-19 SCREWS: 11-13 IN-LB [1.24-1.46 N-m].
#4-20 SCREWS: 4-9 IN-LB [.45-1.01 N-m].
VALUES VALID FOR PLASTITE 48 SCREWS ONLY.

4. RECOMMENDED MOUNTING SCREWS (NOT INCLUDED): CAMCAR PLASTITE 48, SINGLE HELIX.
3. THIS RECEPTACLE MATES WITH DT06-12SX PLUG (X = A,B,C,D KEYS, XXXX = ALL MODIFICATIONS).
2. CONTACT PLATING - MATING SIDE: NICKEL; PCB SIDE: TIN

- 1 MATERIALS:
HOUSING & PIN ALIGNMENT PLATE: PA46 GF30 (SEE SHEET 2 FOR COLORS)
FLANGE SEAL: VMQ (RED-ORANGE)
PIN CONTACTS: COPPER ALLOY

NOTES:

TE INTERNAL PN	DEUTSCH PN
DT15-12PA	DT15-12PA
DT15-12PB	DT15-12PB
DT15-12PC	DT15-12PC
DT15-12PD	DT15-12PD

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. BURKE 08JUN2001	TE Connectivity			
DIMENSIONS: in [mm]		CHK K. MCKEE 03JUL2014				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. MEYER 03JUL2014	NAME RECEPTACLE HEADER			
0 PLC ±-		PRODUCT SPEC 108-151009	12 PIN 180 DEG. DT SERIES			
1 PLC ±		APPLICATION SPEC -	SIZE CAGE CODE DRAWING NO RESTRICTED TO			
2 PLC ±		WEIGHT 33.4 (g)	A2 4AFU8 C=DT15-12PX			
3 PLC ± .025 [0.64]		CUSTOMER DRAWING	SCALE 2:1 SHEET 1 OF 3 REV D			
4 PLC ±						
ANGLES ±0°30'0						
FINISH -						

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

D

C


C

B

B

A


A



8 RECOMMENDED PANEL CUTOUTS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. BURKE 08JUN2001	TE Connectivity		
DIMENSIONS: in [mm]		CHK K. MCKEE 03JUL2014			
		APVD D. MEYER 03JUL2014	NAME RECEPTACLE HEADER 12 PIN 180 DEG. DT SERIES		
		PRODUCT SPEC 108-151009	SIZE A2	CAGE CODE 4AFU8	DRAWING NO DT15-12PX
MATERIAL 		APPLICATION SPEC -	WEIGHT 33.4 (g)	RESTRICTED TO -	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ± 2 PLC ± 3 PLC ±.025 [0.64] 4 PLC ± ANGLES ±0°30'0" FINISH -		CUSTOMER DRAWING	SCALE 2:1	SHEET 2 OF 3	REV D

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
in [mm]

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±.025 [0.64]
4 PLC ±-
ANGLES ±0°30'0"
FINISH -

DWN P. BURKE 08JUN2001
CHK K. MCKEE 03JUL2014
APVD D. MEYER 03JUL2014

PRODUCT SPEC
108-151009

APPLICATION SPEC
-

WEIGHT
33.4 (g)

CUSTOMER DRAWING

TE Connectivity

NAME
RECEPTACLE HEADER
12 PIN 180 DEG.
DT SERIES

SIZE
A2

CAGE CODE
4AFU8

DRAWING NO
C-DT15-12PX

RESTRICTED TO
-

SCALE
2:1

SHEET
3 OF 3

REV
D