





(1,27 mm) .050"

FFMD-20-T-02.00-01-N-R



FFMD-10-S-10.00-01



FFMD SERIES

TIGER EYE™ FLAT IDC WIRE CABLES

Mates with:
FLE*, SFMC*,
Transfer End Option
Mates with: FTS, FTSH,
EHF, SHF, ESHF

SPECIFICATIONS

For complete specifications
see www.samtec.com?FFMD

Insulator Material:
Black Glass Filled Polyester

Terminal:
Phosphor Bronze

Contact:
BeCu (-T)

Plating:
Sn over 50µ" (1,27 µm) Ni

Wire: 30 AWG

Current Rating:
1.8 A per pin
(6 adjacent pins powered)

Operating Temp Range:
-40°C to +105°C

RoHS Compliant:
Yes

RECOGNITIONS

For complete scope of
recognitions see
www.samtec.com/quality




ALSO AVAILABLE (MOQ Required)


- Other sizes
- Contact Samtec.

***Note:** Standard FFMD callout
will not mate with FLE, SFMC.
Must use gold plated callouts.
(See drawing on web.)
When mated with a socket,
Wire 1 mates with Pin 2;
Wire 2 mates with Pin 1, etc.

Note: This Series is
non-standard, non-returnable.



FFMD = Terminal Strip



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM