

AMPHENOL RF PART NUMBER

031-30220-3

BNC Straight Clamp Plug for RG-59 and Belden 9269, 50 Ohm



PRODUCT OVERVIEW

RF Connector, BNC Straight Clamp Plug for RG-59 and Belden 9269, 50 Ohm

Product Type	Connectors
Product Series	BNC
Status	Active

PRODUCT SPECIFICATIONS

Gender	Plug
Orientation	Straight
Termination Style	Cable - Crimp
Impedence (Ohms)	50
Body Finish	Nickel
Body Material	Brass
Contact Finish	Silver
Contact Material	Brass
Contact Termination Style	Solder
Insulator Material	PTFE
Cable Group	E
Cable Type	Belden 8241, Belden 8263, Belden 8279, Belden 9209, RG-140, RG-210, RG-59, RG-59B, RG-62
Crimp Tool	CTL-8
Coupling Mechanism	Bayonet
Max Frequency (GHz)	4
Polarity	Standard

Min. Temp. (Celsius)	-65
Max. Temp. (Celsius)	165
Mating Cycles	500

PRODUCT COMPLIANCE

Product compliance documentation, if available is listed below:

RoHS 2 (EU)	Compliant with Exemption 6C
-------------	-----------------------------