

Catamount® Cable Fastening Systems

Catamount® Cable Ties

Catamount® Ties and Terminals fit the needs of general-purpose fastening and wire terminations. Installers quickly discover that Catamount products offer durable and value-priced cable bundling for a variety of commercial and residential construction applications. Electricians can also take advantage of other benefits in stocking Catamount products in their toolboxes, such as more terminals per bag in most popular sizes than leading comparable brands.

Catamount Ties and Terminals are offered in a wide range of sizes, styles and colors and meet listing requirements for most electrical termination and fastening projects. A choice of matching tools are also offered to provide quick and reliable installations.

Miniature — Series 18



CAT. NO.	LENGTH (IN.)	MAX. BUNDLE DIA.	COLOR	STD. QTY.
L-4-18-9-C	4.0	5/8	Natural	100
L-4-18-0-C	4.0	5/8	Black	100
L-6-18-9-C	6.4	1 1/8	Natural	100
L-6-18-0-C	6.4	1 1/8	Black	100
L-8-18-9-C	8.0	2	Natural	100
L-8-18-0-C	8.0	2	Black	100

Bulk packages available. Contact Customer Service.

Use QC-100, L-200, L-400-C or ERG-50 Installation Tools

Intermediate — Series 30



CAT. NO.	LENGTH (IN.)	MAX. BUNDLE DIA.	COLOR	STD. QTY.
L-5-30-9-C	5.6	1 1/4	Natural	100
L-5-30-0-C	5.6	1 1/4	Black	100
L-8-40-9-C	8.5	2	Natural	100
L-8-40-0-C	8.5	2	Black	100
L-11-40-9-C	11.5	3	Natural	100
L-11-40-0-C	11.5	3	Black	100
L-14-40-9-C	14.5	4	Natural	100
L-14-40-0-C	14.5	4	Black	100

Bulk packages available. Contact Customer Service.

Use QC-100, L-200, L-400-C or ERG-50 Installation Tools

Standard — Series 50



CAT. NO.	LENGTH (IN.)	MAX. BUNDLE DIA.	COLOR	STD. QTY.
L-5-50-9-C	5.5	1	Natural	100
L-5-50-0-C	5.5	1	Black	100
L-7-50-0-C	7.5	1 3/4	Black	100
L-7-50-9-C	7.5	1 3/4	Natural	100
L-11-50-9-C	11.1	3	Natural	100
L-11-50-0-C	11.1	3	Black	100
L-14-50-9-C	14.1	4	Natural	100
L-14-50-0-C	14.1	4	Black	100

Bulk packages available. Contact Customer Service.

Use QC-100, L-200, L-400-C or ERG-50 Installation Tools

Heavy-Duty — Series 120



CAT. NO.	LENGTH (IN.)	MAX. BUNDLE DIA.	COLOR	STD. QTY.
L-8-120-9-C	8.0	2	Natural	100
L-8-120-0-C	8.0	2	Black	100
L-11-120-9-C	11.1	3	Natural	100
L-11-120-0-C	11.1	3	Black	100
L-14-120-9-C	14.2	4	Natural	100
L-14-120-0-C	14.2	4	Black	100
L-18-120-9-L	18.0	4 3/4	Natural	50
L-18-120-0-L	18.0	4 3/4	Black	50
L-24-120-9-L	24.2	7	Natural	50
L-24-120-0-L	24.2	7	Black	50
L-28-120-9-L	28.0	9	Natural	50
L-28-120-0-L	28.0	9	Black	50

Use L-300C or ERG-120 Installation Tool

Extra Heavy-Duty — Series 175



CAT. NO.	LENGTH (IN.)	MAX. BUNDLE DIA.	COLOR	STD. QTY.
L-24-175-9-L	24.0	7.2	Natural	50
L-24-175-0-L	24.0	7.2	Black	50
L-34-175-9-L	34.0	10	Natural	50
L-36-175-9-L	36.0	10 3/4	Natural	50
L-36-175-0-L	36.0	10 3/4	Black	50
L-41-175-9-L	41.0	12	Natural	50
L-41-175-0-L	41.0	12	Black	50
L-48-175-9-L	48.0	15	Natural	50
L-48-175-0-L	48.0	15	Black	50

Use L-300C Installation Tool

Identification Ties




CAT. NO.	LENGTH (IN.)	MAX. BUNDLE DIA.	COLOR	STD. QTY.
L-7-50ID-9-C	7.875	1 1/4	Natural	100
L-4-18ID-9-C	4.0	5/8	Natural	100

Bulk packages available. Contact Customer Service.

Use QC-100, L-200 or L-400-C Installation Tool

Sample Catalog Order:

Color Table



4" Length, 18-lb. Tensile Strength, Natural Color, 100-Pack Quantity

0 – Black (UV Resistant)	9 – Natural
1 – Brown	11 – Fluorescent Pink
2 – Red	16 – Fluorescent Orange
3 – Orange	17 – Fluorescent Yellow
4 – Yellow	18 – Fluorescent Green
5 – Green	20 – Fluorescent Blue
6 – Blue	
7 – Purple	
8 – Gray	

Catamount® Cable Ties



Releasable Ties



CAT. NO.	LENGTH (IN.)	MAX. BUNDLE DIA.	COLOR	STD. QTY.
L-5-50R-9-C	5.9	¼	Natural	100
L-5-50R-0-C	5.9	¼	Black	100
L-8-50R-9-C	7.8	2	Natural	100
L-8-50R-0-C	7.8	2	Black	100
L-10-50R-9-C	11.265	3	Natural	100
L-10-50R-0-C	11.265	3	Black	100

Bulk packages available. Contact Customer Service. Push button release.



Push Mount Cable Ties



CAT. NO.	LENGTH (IN.)	MOUNTING HOLE	MAX. PANEL THICKNESS	MAX. BUNDLE DIA.	COLOR	STD. QTY.
L-5-50PM-9-C	5.8	.250	.105	1	Natural	100
L-5-50PM-0-C	5.8	.250	.105	1	Black	100
L-7-50PM-9-C	8.2	.250	.105	1½	Natural	100
L-7-50PM-0-C	8.2	.250	.105	1½	Black	100

Bulk packages available. Contact Customer Service.

Use QC-100, L-200, L-400-C Installation Tool

Black shown



Mounting Head Ties

CAT. NO.	LENGTH (IN.)	MAX. BUNDLE DIA.	WIDTH (IN.)	MIN. LOOP TENSILE	MOUNTING HEAD SCREW SIZE	COLOR	STD. QTY.
L-5-30MH-9-C	5.85	1¼	.140	30	No. 8	Natural	100
L-5-30MH-0-C	5.85	1¼	.140	30	No. 8	Black	100
L-7-50MH-9-C	7.5	1½	.185	30	No. 10	Natural	100
L-7-50MH-0-C	7.5	1½	.185	30	No. 10	Black	100
L-11-50MH-9-C	11.1	3	.187	50	No. 10	Natural	100
L-11-50MH-0-C	11.1	3	.187	50	No. 10	Black	100
L-14-50MH-9-C	14.5	4	.187	50	No. 10	Natural	100
L-14-50MH-0-C	14.5	4	.187	50	No. 10	Black	100
L-14-120MH-9-C	14.85	4	.300	120	¼"	Natural	100
L-14-120MH-0-C	14.85	4	.300	120	¼"	Black	100

Bulk packages available. Contact Customer Service. Use QC-100, L-200, L-400-C, ERG-120 or ERG-50 Installation Tool

Releasable Push Mount Cable Ties



CAT. NO.	LENGTH (IN.)	MOUNTING HOLE	MAX. PANEL THICKNESS	MAX. BUNDLE DIA.	COLOR	STD. QTY.
L-5-50PMR-9-C	5.8	.250	.105	1	Natural	100
L-5-50PMR-0-C	5.8	.250	.105	1	Black	100
L-7-50PMR-9-C	8.2	.250	.105	1½	Natural	100
L-7-50PMR-0-C	8.2	.250	.105	1½	Black	100

Bulk packages available. Contact Customer Service.


Use QC-100, L-200, L-400-C Installation Tool

Tail twists right off — no tools needed!

TwistTail™



NEW!



- Unique, patent-pending design for quick, easy, tool-less installation
- After installing, remove excess tail with a simple "bend, bend again and twist" motion
- Tail breaks off neat and clean — no sharp edges to damage hands or cables
- Ideal for limited-space installations where you can't fit a cut-off tool
- Suitable for any general-purpose cable tie application
- Available in white or UV resistant black 6.6 nylon

CAT. NO.	LENGTH (IN.)	MIN. TENSILE STRENGTH (LBS.)	COLOR	STD. QTY.
TT-7-50-9-C	7	50	White	100
TT-7-50-0-C	7	50	Black	100
TT-11-50-9-C	11	50	White	100
TT-11-50-0-C	11	50	Black	100
TT-14-50-9-C	14	50	White	100
TT-14-50-0-C	14	50	Black	100

Catamount® Cable Fastening Systems

Catamount® Cable Ties

Catamount® Cable Tie Assortment Packages

- Natural nylon or black weather-resistant nylon
- Reusable jar
- Easily merchandised
- Great value
- Two size combinations and quantities



90650 and 90650-IUV



Cable Tie Jar

CAT. NO.	LENGTH (IN.)	WIDTH	MAX. BUNDLE (IN.)	TENSILE STRENGTH	MATERIAL	JAR QTY.
90457-I	4	.100	¾ (.625)	18#	Natural Nylon	200
	5.6	.130	1¼ (1.25)	30#		100
	7.5	.187	1¾ (1.75)	50#		200
90457-IUV	4	.100	¾ (.625)	18#	Black Weather-Resistant Nylon	200
	5.6	.130	1¼ (1.25)	30#		100
	7.5	.187	1¾ (1.75)	50#		200
90650-I	4	.100	¾ (.625)	18#	Natural Nylon	300
	7.5	.187	1¾ (1.75)	50#		300
	11.1	.187	3	50#		50
90650-IUV	4	.100	¾ (.625)	18#	Black Weather-Resistant Nylon	300
	7.5	.187	1¾ (1.75)	50#		300
	11.1	.187	3	50#		50

Cable Tie Assortments — Natural Nylon




CAT. NO.	CONTENTS	QTY.	BAGS/CASE
CAT-711	L-7-50-9-C	100	25
	L-11-50-9-C	50	
CAT-4811	L-4-18-9-C	100	35
	L-8-40-9-C	100	
	L-11-50-9-C	50	
CAT-5811	L-5-30-9-C	200	35
	L-8-40-9-C	200	
	L-11-50-9-C	50	

For UV Black assortments, add -B to Catalog Number.

Cable Tie Mounting Bases

- ¾" and 1" mounts for use with 18# through 50# tensile cable ties
- Supplied on rubber-based or acrylic closed cell foam adhesive or with no adhesive for #6 screw mount applications
- Available in 6.6 Natural Nylon and 6.6 Black Nylon
- UL® Flammability 94 V-2 (clip)



Cat. No.	MOUNT METHOD	COLOR
¾" Class		
MPNY-750-9-C	Synthetic Rubber Adhesive	Natural
MPNY-750-0-C	Synthetic Rubber Adhesive	Black
MPNY-750A-9-C	Acrylic Adhesive	Natural
MPNY-750A-0-C	Acrylic Adhesive	Black
MPNY-750S-9-C	#6 Screw	Natural
MPNY-750S-0-C	#6 Screw	Black
1" Class		
MPNY-1000-9-C	Synthetic Rubber Adhesive	Natural Nylon
MPNY-1000-0-C	Synthetic Rubber Adhesive	Black Nylon
MPNY-1000A-9-C	Acrylic Adhesive	Natural Nylon
MPNY-1000A-0-C	Acrylic Adhesive	Black Nylon
MPNY-1000S-9-C	#6 Screw	Natural Nylon
MPNY-1000S-0-C	#6 Screw	Black Nylon

For use with 18–50 lb. Cable Ties

- Mounting Surface should be cleaned with alcohol based (IPA) cleaner before application
- Acrylic Based may be repositioned initially. Allow 24–72 hours setup for maximum performance with Acrylic Based adhesives
- For Rubber Based, allow 15 minutes setup for maximum performance

Catamount® Terminals



Vinyl Insulated Ring Terminals



CAT. NO.	WIRE RANGE	BOLT SIZE	PKG. QTY.
TV18-6R	22-16	#6	50
TV18-8R		#8	50
TV18-10R		#10	50
TV18-14R		1/4"	50
TV18-516R		5/16"	50
TV14-6R	16-14	#6	50
TV14-8R		#8	50
TV14-10R		#10	50
TV14-14R		1/4"	50
TV14-516R		5/16"	50
TV10-6R	12-10	#6	25
TV10-8R		#8	25
TV10-10R		#10	25
TV10-14R		1/4"	25
TV10-516R		5/16"	25
TV8-8R	8 AWG	#8	10
TV8-10R		#10	10
TV8-14R		1/4"	10
TV8-516R		5/16"	10
TV8-38R		3/8"	10
TV6-10R	6 AWG	#10	10
TV6-14R		1/4"	10
TV6-516R		5/16"	10
TV6-38R		3/8"	10
TV6-12R		1/2"	10

*8 AWG 25 to a package **6 AWG 10 to a package



Non-Insulated Ring Terminals

CAT. NO.	WIRE RANGE	BOLT SIZE	PKG. QTY.
T18-6R	22-16	#4-#6	50
T18-8R		#8	50
T18-10R		#10	50
T14-6R	16-14	#6	50
T14-8R		#8	50
T14-10R		#10	50
T10-6R	12-10	#6	25
T10-8R		#8	25
T10-10R		#10	25
T10-14R		1/4"	25

Vinyl Insulated Fork Terminals

CAT. NO.	WIRE RANGE	BOLT SIZE	PKG. QTY.
TV18-6F	22-16	#6	50
TV18-8F		#8	50
TV18-10F		#10	50
TV18-14F		1/4"	50
TV14-6F	16-14	#6	50
TV14-8F		#8	50
TV14-10F		#10	50
TV14-14F		1/4"	50
TV10-6F	12-10	#6	25
TV10-8F		#8	25
TV10-10F		#10	25
TV10-14F		1/4"	25
TV10-516F		5/16"	25



Non-Insulated Fork Terminals

CAT. NO.	WIRE RANGE	BOLT SIZE	PKG. QTY.
T18-6F	22-16	#6	50
T18-8F		#8	50
T18-10F		#10	50
T14-6F	16-14	#6	50
T14-8F		#8	50
T14-10F		#10	50
T10-6F	12-10	#6	25
T10-8F		#8	25
T10-10F		#10	25
T10-14F		1/4"	25



Vinyl Insulated Locking Fork Terminals

CAT. NO.	WIRE RANGE	BOLT SIZE	PKG. QTY.
TV18-6LF	22-16	#6	50
TV18-8LF		#8	50
TV18-10LF		#10	50
TV14-6LF	16-14	#6	50
TV14-8LF		#8	50
TV14-10LF		#10	50
TV10-6LF	12-10	#6	25
TV10-8LF		#8	25
TV10-10LF		#10	25

Non-Insulated Locking Fork Terminals

CAT. NO.	WIRE RANGE	BOLT SIZE	PKG. QTY.
T18-6LF	22-16	#6	50
T18-8LF		#8	50
T18-10LF		#10	50
T14-6LF	16-14	#6	50
T14-8LF		#8	50
T14-10LF		#10	50
T10-6LF	12-10	#6	25
T10-8LF		#8	25
T10-10LF		#10	25



Vinyl Insulated Butt Splices

CAT. NO.	WIRE RANGE	PKG. QTY.
TV18-BS	22-18	50
TV14-BS	16-14	50
TV10-BS	12-10	25



Nylon Wire Joints

CAT. NO.	WIRE RANGE	STD. PKG.
TN18-WJ	22-16	50
TN14-WJ	16-14	50
TN10-WJ	12-10	25



Multiple Quick Splices

CAT. NO.	WIRE RANGE	PKG. QTY.
TV18-00QS	22-16	50
TV14-00QS	16-14	50
TV10-00QS	12-10	25

Sta-Kon Terminal Products and Tools

Catamount® Terminals

Vinyl Insulated Female Disconnects — 250 Series

CAT. NO.	WIRE RANGE	PKG. QTY.
TV18-250FD	22-16	50
TV14-250FD	16-14	50
TV10-250FD	12-10	25

Nylon Fully Insulated Female Disconnects — 250 Series

CAT. NO.	WIRE RANGE	PKG. QTY.
TNF18-250FD	22-16	50
TNF14-250FD	16-14	50
TNF10-250FD	12-10	25

Vinyl Fully Insulated Female Disconnects — 250 Series

CAT. NO.	WIRE RANGE	PKG. QTY.
TVF18-250FD	22-16	50
TVF14-250FD	16-14	50
TVF10-250FD	12-10	25

Vinyl Insulated Male Disconnects — 250 Series

CAT. NO.	WIRE RANGE	PKG. QTY.
TV18-250MD	22-16	50
TV14-250MD	16-14	50
TV10-250MD	12-10	25

Nylon Fully Insulated Male Disconnects — 250 Series

CAT. NO.	WIRE RANGE	PKG. QTY.
TNF18-250MD	22-16	50
TNF14-250MD	16-14	50
TNF10-250MD	12-10	25

Vinyl Insulated Piggyback Disconnects — 250 Series

CAT. NO.	WIRE RANGE	PKG. QTY.
TV18-250PD	22-16	50
TV14-250PD	16-14	50
TV10-250PD	12-10	25

Vinyl Fully Insulated Female Bullet Connectors — 4mm (.156")

CAT. NO.	WIRE RANGE	PKG. QTY.
TVF18-4FB	22-16	50

Nylon Fully Insulated Female Bullet Connectors

CAT. NO.	WIRE RANGE	PKG. QTY.
TNF18-4FB	22-16	50
TNF14-4FB	16-14	50

Vinyl Insulated Straight Blade Terminals

CAT. NO.	WIRE RANGE	PKG. QTY.
TV18-10BL	22-16	50
TV18-18BL		50
TV14-10BL	16-14	50
TV14-18BL		50
TV10-10BL	12-10	25

Vinyl Insulated Male Bullet Connectors — 4mm (.156")

CAT. NO.	WIRE RANGE	PKG. QTY.
TV18-4MB	22-16	50
TV14-4MB	16-14	50

Fully Insulated Nylon Male Bullet Connectors

CAT. NO.	WIRE RANGE	PKG. QTY.
TNF18-4MB	22-16	50
TNF14-4MB	16-14	50

Vinyl Insulated Straight Pin Terminals

CAT. NO.	WIRE RANGE	PKG. QTY.
TV18-12PT	22-16	50
TV14-12PT	16-14	50
TV10-14PT	12-10	25

Thomas & Betts

www.tnb.com

United States
Tel: 901.252.8000
800.816.7809
Fax: 901.252.1354

Canada
Tel: 450.347.5318
Fax: 450.347.1976

Technical Services
Tel: 888.862.3289

Catamount® Terminal Tools



WT111M



WT112M



ERG1-WS



CM2000A



TBM6S

CAT. NO.	DESCRIPTION	PKG. QTY.
WT111M	Plier tool with cutter for 22–10 AWG non-insulated terminals	1
WT112M	Plier tool with cutter for 22–10 AWG insulated and non-insulated terminals, splices and disconnects	1
TBM6S	Toggle Type Hand Tool with Shure-Stake® for 8–6 AWG, vinyl insulated terminals (dies sold separately)	1
ERG1-WS	Ergonomic Wire Stripping Tool	1
CM2000A	10" Ratchet Crimping Tool for insulated terminals (22–10 AWG)	1