



Product information

Erem®

530E15A

Code No. : **T530E15A**

Distance cutter

- Special tool steel
- ESD-safe
- Variable cutting length
- With protective stop screw

Technical Data

Cut:	Flush
Length:	120 mm / 4,724 Inch
Weight:	70 g / 2.47 oz.
Jaw length:	20 mm / .787 Inch
Width of tips:	4,5 mm / .177 Inch
Cutting length (variable):	1,2 - 6 mm /.047 - .236 Inch
Max. cutting capability	
Copper wire:	Ø 1.2 mm / .047 Inch

Distance cutters

- Erem distance cutters are available with fixed and variable cutting lengths
- The tips are polished so as to prevent board damage
- For cutting wires to the right length and for fixing components

Erem Cutters and Tip Cutters

- Internal patented Erem Magic Spring
 - Reduce costs by long life
 - Constant spring force
 - Guarantees more than 1 million operations
- High precision screw joint

- Smooth jaw action with no play
- Smooth cutting operation with no jaw overlapping
- Induction-hardened cutting edges in Rockwell hardness 63 - 65 HRc for exceptionally long life
- EMOS maximum opening stop limits the cutting-edge tips from opening more than 5 mm / .197 Inch. The limited extent to which the handles can open prevent user hand fatigue.
- Ergonomically shaped handles for high comfort, better grip and added safety
- Erem cut:
Options for semi flush, full flush or super flush cuts