




1. Insulator Material: Nylon-6T, UL94V-0, Color: Black
2. Contact Material: Phosphor Bronze
3. Contact Plating: Gold Plated Over Nickel
4. Current Resistance: 1Amp AC/DC
5. Contact Resistance: 20m ohms Max.
6. Insulation Resistance: 5000M ohms Min.
7. Dielectric Withstanding Voltage: 500V AC/minute.
9. Operation Temperature: -40°C to +105°C
10. RO=RoHS



Recommended P.C.B Layout

PART NO.	TITLE	A	B	Contact Plated
15350180	TSI-02SG-R0	2.00	4.60	Gold Flash Plated
15350190	TSI-03SG-R0	4.00	6.60	Gold Flash Plated
15350200	TSI-06SG-R0	10.00	12.60	Gold Flash Plated
15350210	TSI-04SG-R0	6.00	8.60	Gold Flash Plated
15350220	TSI-04SG6-R0	6.00	8.60	30u' Gold Plated
15350230	TSI-04SG4-R0	6.00	8.60	15u' Gold Plated
15350240	TSI-40SG-R0	78.00	80.60	Gold Flash Plated
15350250	TSI-10SG-R0	18.00	20.60	Gold Flash Plated
15350260	TSI-32SG-R0	62.00	64.60	Gold Flash Plated
15350270	TSI-11SG-R0	20.00	22.60	Gold Flash Plated

[illegible]