




DIN 7985 A

~ISO 7045

4.8

Standard withdrawn



BN 384

Phillips pan head machine screws

form H

Steel 4.8

zinc plated blue

- ~UNI 7687
- ~ČSN 021147



All lengths fully threaded

Article#	d ₁	d ₂ max.	k max.		m~	t min.	t max.	L
3056354	M1,6	3,2	1,42	0	1,8	0,72	1,02	2
1944843								3
1944940								4
1945025								5
1945130								6
1945319								8
3056355	M2	4	1,72	1	2,5	1,1	1,4	2
1154087								3
1154095								4
1154109								5
1154117								6
1154125								8
1154133								10
1154141								12
1135651								16
1135678								20
1154168	M2,5	5	2,12	1	2,7	1,3	1,6	3
1154176								4
1154184								5
1154192								6
1154206								8
1154214								10
1154222								12
1135686								16
1135694								20
1471945								25

Article#	d ₁	d ₂ max.	k max.		m~	t min.	t max.	L
1471953	M2,5	5	2,12	1	2,7	1,3	1,6	30
3056356	M3	6	2,52	1	3,1	1,7	2	3
1435639								4
1154230								5
1154249								6
1154257								8
1154265								10
1154273								12
1154281								(14)
1154303								16
1154311								(18)
1154338								20
1154346								(22)
1154354								25
1154362								30
1135708								35
1135716								40
1471961								45
1471988								50
3056361	(M3,5)	7	2,82	2	4,2	1,74	2,24	5
1154370								6
1154389								8
1154397								10
1154400								12
1154427								16
1154443								20
1154478								25
1154486								30
2096749	M4	8	3,25	2	4,6	2,04	2,54	4
1135724								5
1154494								6
1154508								8
1154516								10
1154524								12
1154532								(14)
1154540								16
1154559								(18)
1154567								20
1154575								(22)
1154583								25
1154591								30

Article#	d ₁	d ₂ max.	k max.		m~	t min.	t max.	L
1154605	M4	8	3,25	2	4,6	2,04	2,54	35
1154613								40
1135732								45
1135740								50
1471996								60
1472003								70
1472011								80
2096757	M5	10	3,95	2	5,3	2,77	3,27	5
1154621								6
1154648								8
1154656								10
1154664								12
1154672								(14)
1154680								16
1154699								(18)
1154702								20
1154710								(22)
1154729								25
1154737								30
1154745								35
1154753								40
1154761								45
1154788								50
1472038								60
1472046								70
1472054								80
3056363	M6	12	4,75	3	6,8	3,03	3,53	6
1154796								8
1154818								10
1154826								12
1154834								(14)
1154842								16
1154850								(18)
1154869								20
1154877								(22)
1154885								25
1154893								30
1154907								35
1154915								40
1154923								45
1154931								50

Article#	d ₁	d ₂ max.	k max.		m~	t min.	t max.	L
1472062	M6	12	4,75	3	6,8	3,03	3,53	60
1472070								70
1472089								80
3056366	M8	16	6,15	4	9	4,18	4,68	10
1122363								12
1122398								16
1122428								20
1122444								25
1122452								30
1122460								35
1122479								40
1122487								45
1122495								50
1472097								60
1472100								70
1472119								80
1122525	M10	20	7,68	4	10,2	5,38	5,88	16
1122541								20
1122576								25
1122584								30
1122592								35
1122606								40
1122614								45
1122630								60