

NOTES: UNLESS OTHERWISE SPECIFIED

1. CONSTRUCTION:



HOUSING: NYLON 6,6 33% GLASS FILLED.
AVAILABLE IN BLK OR RED.
FRAME: BRASS. NICKEL PLATED.
CONTACT: BeCu OR PHOSPHOR BRONZE. NICKEL PLATED.

HARDWARE: BLACK OXIDE STEEL WIRE CLAMPING
SET SCREW. STAINLESS STEEL HOUSING
CLAMPING NUT & SCREW.

2. PERFORMANCE:

MAXIMUM CURRENT: 3.0 AMPS
MAXIMUM VOLTS: 1400 VRMS
MAXIMUM TEMPERATURE: 167°F (75°C)

3. FEATURES:
AVAILABLE WITH RESISTOR.



		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES		CONTRACT NO.		DESCRIPTION	
		± .XX ± .XXX ±	±	APPROVALS	DATE	E-Z-HOOK [®] DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A.	
				DRAWN	R.L.		
				APPROVED BY	9/10		
		MATERIAL SEE NOTE.				STK DOUBLE BANANA PLUG	
		FINISH SEE NOTE.					
		USED ON					
		APPLICATION		DO NOT SCALE DRAWING		SIZE	REV.
						CODE IDENT NO.	DRAWING NO.
						A 08505	DB750
						SCALE	SHEET 1 OF 1
						1:1	