



Sample photo

Order symbol: PC 122008
Product nbr: 7032760
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074003676
El. number:
 Finland 3423438
 Denmark 8212002843
 Italy 7301045
 Sweden 2536125

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:		L	W	H	Rating:
mm:		120	200	75	Ingress Protection (EN 60529): IP 66/67 Impact Resistance (EN 50102): IK 08/07 Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): Yes UV resistance: UL 508 Flammability Rating (UL 746 C 5): UL 94 5V Glow Wire Test (IEC 695-2-1) °C: 960 NEMA Class: NEMA 1, 4, 4X, 12, 13
inch:		4.7	7.9	3	
Materials:					
Material:		PC			
Base colour:		RAL 7035			
Cover colour:		RAL 7035			
Cover screws material:		Stainless steel			
Gasket material:		Polyurethane			
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
TM 1216		Mounting plate			
TM 1220		Mounting plate			
MIV 10		DIN-35 Mounting rail			
TRH 1220		DIN-35 Mounting rail			
Certificates:					
Underwriters Laboratories					
Fimko					
Europe EN 50298 1998					
UL Canada					
Gost R					

