



FEATURES:

- Mates with Model #'s 4771, 4772 or 4741 square pin receptacles.
- The rotating Micrograbber® Test Clip is ideal for testing surface mounted devices (SMDs), high density leads with 1.2 (0.05) spacing, and fine gauge wires 0.1 (0.004).
- Two access entries with 0.6 (.025) square pins.
- Rotating pincers grasp leads firmly.
- Extended guide tube reaches into tight areas and can be bent to a 35° angle.

MATERIALS:

Insulation: Nylon

Wire: Steel

RATINGS:

Operating Temperature: +80°C. (+176°F.) Max.

Operating Voltage: 30VAC/60VDC

Current: 2 Amperes Max.

ORDERING INFORMATION: Model 5790-*

*=Color, -0 Black, -2 Red

Ordering Example: 5790-2 Color is Red

ORDERING INFORMATION: Model 5929-*

-0 Kit contains 10 Model 5790 Black clips.

-2 Kit contains 10 Model 5790 Red clips.

ORDERING INFORMATION: Model 5930

Kit contains 5 Black & 5 Red Model 5790 clips.

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02"$ (.51 mm), .xxx = $\pm .005"$ (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA