



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: INTERNET350U

Internet Office 350VA Ultra-compact Standby 120V UPS with USB port



Highlights

- 350VA ultra-compact UPS
- Maintains 120V nominal output during blackouts
- Workstation optimized features include HID-compliant USB port, single line TEL / DSL line surge suppression and three surge only outlets
- 99% line-mode efficiency saves energy and operating costs
- Input: NEMA 5-15P (120V 15A) / Output: 6 NEMA 5-15R (120V)
- 3 year product warranty / \$100,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

Description

Tripp Lite's INTERNET350U standby UPS system offers complete protection from blackouts, brownouts and transient surges on both AC and dialup modem lines. Provides seamless battery support during brownouts and power failures with enough runtime to save and shutdown connected equipment without data loss. Offers complete power protection in an ultra-compact, flat-pack housing with an appearance closer to a power strip than other bulky UPS designs. Includes 3 battery supported outlets for computer, monitor and one vital system peripheral, plus 3 additional surge suppression-only outlets for printers and other system accessories not requiring battery support. USB port enables optional unattended system shutdown without data loss in the case of extended power failure. PowerAlert software available via free download from www.tripplite.com, includes bundled USB cable. Built-in single line RJ11 phone suppression jacks with line splitter protects up to two directly connected modems, fax machines, cordless phones or other peripherals with a standard dialup phone connection. Built-in audible alarm and front panel LEDs offer continuous status information regarding line and battery power operation. 350VA/180 watt power handling ability supports entry-level PC systems for up to 15 minutes during power fail conditions. 3 year warranty. \$100,000 [connected equipment insurance](#) (USA, Puerto Rico, & Canada Only).

Package Includes

- INTERNET350U UPS System
- USB communications cable
- Instruction manual with warranty information

Features

- INTERNET350U standby UPS offers complete protection from blackouts, brownouts and surges on both AC and TEL/DSL line connections
- 6 widely spaced outlets accommodate large transformer plugs without blocking outlets
- 3 battery supported outlets protect computer, monitor and vital system peripherals, plus 3 additional surge suppression-only outlets for printers and other system accessories not requiring battery support
- Provides battery derived AC output during blackouts and brownouts
- 350VA/180 watt power handling ability supports a variety of PCs, workstations and other sensitive electronics
- Supports entry-level PC systems up to 12 minutes during blackout conditions
- Built-in single line TEL/DSL line surge suppression protects modems, fax machines or cordless phones on a single phone line connection
- USB port, free PowerAlert software (available via web download) and cabling offer safe unattended shutdown without data loss during extended outages
- HID-compliant USB interface enables integration with built-in power management and auto-shutdown features of Windows and Mac OS X.

- Supports Tripp Lite's Watchdog system service to restore operation to locked equipment through soft reboot of application/OS or hard power off/on reboot of connected equipment - ideal for unattended kiosk applications
- Space saving, ultra-compact housing fits almost anywhere

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	350
Output Watt Capacity (watts)	180
Nominal Output Voltage(s) Supported	115V; 120V
Frequency compatibility	60 Hz
Output voltage regulation (Battery mode)	115V (+/- 5%)
Built-in UPS output receptacles	6 5-15R outlet(s)
Surge suppression only outlets	3 UPS outlets, 3 surge-only outlets
Output AC waveform (AC mode)	Sine wave
Output AC waveform (battery mode)	PWM sine wave
INPUT	
Rated input current (at maximum load)	10A
Nominal Input Voltage(s) Supported	120V AC
UPS input connection type	5-15P
UPS Input cord length (ft.)	6
UPS Input cord length (m)	1.8
Recommended Electrical Service	15A 120V
BATTERY	
Full load runtime (minutes)	3 minutes (180w)
Half load runtime (minutes)	11 minutes (90w)
DC system voltage (VDC)	12
LEDS ALARMS & SWITCHES	
LED Indicators	2 LEDs indicate power status and overload/check battery status
Alarms	Audible alarm indicates power-failure and overload status
Switches	Combination switch controls on/off power status and self-test operation
SURGE / NOISE SUPPRESSION	
UPS AC suppression joule rating	380 joules

EMI / RFI AC noise suppression	Yes
PHYSICAL	
Installation form factors supported with included accessories	Tower; Ultra-compact desktop; Wallmount (using keyhole mounting tabs)
Primary form factor	Desktop
UPS / Power Module dimensions in primary form factor (height x width x depth / inches)	3 x 8 x 6.4
UPS / Power Module dimensions in primary form factor (height x width x depth / cm)	7.5 x 20.4 x 16.1
UPS / Power Module weight (lbs)	5
UPS / Power Module weight (kg)	2.3
UPS Shipping dimensions (height x width x depth / inches)	4.1 x 11.3 x 7.7
UPS Shipping dimensions (height x width x depth / cm)	10.5 x 28.7 x 19.5
Shipping weight (lbs)	5.8
Shipping weight (kg)	2.6
UPS housing material	ABS
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC mode BTU / hr. (full load)	6
Battery mode BTU / hr. (full load)	134.3
COMMUNICATIONS	
Communications interface	USB (HID enabled)
PowerAlert software	Free download from www.tripplite.com
Communications cable	USB interface cable included
WatchDog compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
LINE / BATTERY TRANSFER	
Transfer time	4 milliseconds (AC to battery mode) / 2 milliseconds (Battery to AC mode)
Low voltage transfer to battery power (setpoint)	99

High voltage transfer to battery power (setpoint)	139
SPECIAL FEATURES	
Cold Start (startup in battery mode during a power failure)	Cold-start operation supported
Green & high efficiency features	Greater than 95% efficiency - GREEN UPS
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI)
WARRANTY	
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 connected equipment insurance

Related Items

Optional Products

Product Type	Related Model	Description	Qty.
USB Cables & Adapters	U005-10I	10-inch USB A/A Gold Extension Cable (USB-A Right Angle Male to USB-A Female)	-
Software	WATCHDOGSW	WatchDog Service Monitoring / Reboot Software	-
Audio Cables	CT120	Instant-Read- AC Outlet Circuit Tester	-
Surge Protectors	DNET1	Network Surge Suppressor - Essential protection for data and communication lines	-
USB Hubs/Accessories	U222-004-R	4-Port USB2.0 Ultra-Mini Hub	-
Surge Protectors	DTEL2	Network Surge Suppressor - Essential protection for data and communication lines	-
Extended Warranties	WEXT5-INTERNET	5-Year Extended Warranty - For Internet Office, AVR and ECO Series UPS Systems	-

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=2663.

Copyright © 2010 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.