

## Intelliprint 9035N Range

### Intelligent printing



- A4 High speed Mono Laser Printer for Medium to Large workgroups
- High workload 150,000 pages per month
- Fast 400Mhz Processor for fast document processing
- Intelifilter for Forms Management
- Comprehensive paper handling
- 1200 dpi for quality business documents
- Network ready

### It's Fast

400 Mhz processor speed, the fastest in its class combined with TallyGenicom's market leading Intelliprint controller technology, make the 9035 the most impressive workgroup printer available today. Enough memory as standard to handle any print job, combined with fast 9 seconds first print page print time, make the 9035 the ideal printer for heavy workload applications where short print time is critical.

### Productive Power

Capable of 150,000 pages per month the 9035 is built to last and at 35 pages per minute will more than meet the demands of a busy office. To cope with all this workload the 9035 can be configured with an impressive list of paper handling features including multiple bins and duplex capability making it a true workhorse.

### Intelligent Migration

Legacy Data - no problem. Intelifilter resident within the 9035 enables true migration from other technologies such as a line printer or even SIDM (Serial Impact Dot Matrix). All this without expensive server software lets TallyGenicom solve all your printing problems.

### Secure Printing

Add a disc drive and secure printing is enabled, just input a PIN code in the printer and collect your output. In addition Job Accounting, a Job Library, Collation and the ability to store forms, fonts and logos etc. becomes possible with the Hard Disc option.

---

#### Available Configuration:

**Intelliprint 9035NL** PCL5e/6 version with no internal fonts  
**Intelliprint 9035N** PCL5e/6 version Full Extended Fonts  
**Intelliprint 9035NPS** with Adobe Postscript 3  
**Intelliprint 9035NT** with additional paper tray  
**Intelliprint 9035ND** with Duplex  
**Intelliprint 9035NDT** with Duplex and additional tray

<b>Print Speed</b>	Up to 35 pages per minute letter; 34 pages per minute A4
<b>Print Method</b>	Intelliprint Controller
<b>Processor</b>	R5000 400Mhz
<b>Resolution</b>	1200 x 1200 dpi
<b>Time To 1st Page</b>	Less than 9 Seconds
<b>Memory</b>	64MB expandable to 256MB (2 slots); Optional 20GB (or higher) hard disk
<b>Standard Connectivity</b>	Parallel (Bi directional IEEE 1284), USB (v2.0), Ethernet 10/100baseT (on all models)
<b>Optional Connectivity</b>	1 option slot available; Auto interface switching
<b>Standard Emulation</b>	PCL5e/PCL6
<b>Optional Emulation</b>	Adobe PostScript level 3
<b>Print Monitor</b>	TCP/IP, EtherTalk, Rendezvous, SNMP, Printer MIB, e-mail status, printer monitoring and administration via integrated web browser and TGNAdmin.
<b>Fonts</b>	9035NL uses Windows fonts. Other models have resident fonts
<b>Consumables</b>	Replacement process/toner unit < 17,000 pages*, Fuser < 200,000 pages**, Feed Roller < 200,000 pages** Initial processor/toner unit supplied with printer < 10,000 pages* *Based on 5% coverage of A4 page, **Contained within Maintenance kit
<b>STD Paper Handling</b>	150 sheet Universal Cassette plus 550 sheet universal cassette
<b>Opt'l Paper Handling</b>	3rd universal cassette accepts 550 sheets; 4th universal cassette accepts 550 sheets
<b>Duplexing</b>	Optional
<b>Paper Type</b>	Standard paper, transparencies, labels, heavy paper stock, envelopes, bond, thick media
<b>Paper Weight</b>	Cassettes: 60-216gsm; MPF: 60-216 gsm; Duplex: 60-216 gsm
<b>Paper Size</b>	Cassettes 1 and 2 - Width 98.4 - 215.9mm, Length 148mm - 355.6mm. Legal, Letter, Executive, Statement, A4, B5, 1/3 A4, Postcard, Index card, Officio. Envelopes COM 10, Monarch, C5, DL
<b>Paper Output</b>	500-sheet face-down top output; Optional Cassette: 500-sheet offset catch tray
<b>Physical Weight</b>	20.6 Kg unpacked, 26.8 Kg packed
<b>PhysicalSize</b>	421.8(w) x 465.4(d) x 404.3(h) mm
<b>Power Voltage</b>	EMEA 200-264V, USA 98-132v
<b>Power Frequency</b>	50/60 Hz
<b>Compliance</b>	Energy Star Compliant, Less than 14 Watts in sleep mode, Standby 83 Watts. Less than 350 Watts printing (average)
<b>Workload</b>	Up to 150,000 pages per month. 16,000 - 28,000 pages per month typical use
<b>Reliability MTBF</b>	300,000 pages (Power on 8hr/day in typical duty cycle)
<b>Reliability MTTR</b>	30 minutes
<b>Drivers</b>	Windows 9.x/NT 4.0/2000/XP/ME, MAC PostScript OSX, Linux via PPD
<b>Temperature</b>	Operating: 10° to 32° C)
<b>Humidity</b>	20%-80% Non-Condensing, relative humidity
<b>Acoustic</b>	Printing - 53.6dBA, Stand by - 27dBA, Sleep mode - Background level
<b>Warranty</b>	2 years on site next business day. Installation free of charge, mainland UK & Eire
<b>Note</b>	Exceeding the monthly duty cycle will not void the warranty if TallyGenicom consumables and maintenance kits are used. Toner saver mode providing up to 40% savings. Drum and Fuser Yields will vary based on job run length, media type, size, weight, orientation, and usage patterns.