




Dimensions: mm (In.)



Circuit Diagram

Mouser Stock No.	Button Color
103-7052-EV	Orange
103-7053-EV	Red

Electrical Specifications:

- Rating: 16A/125VAC, 10A/ 250VAC
- Contact Resistance: 50m Ω max.
- Insulation Resistance: 500 VDC 100M Ω min.
- Dielectric Strength: 1500 VAC 1 minute

Mechanical Specifications:

- Circuit: 3P SPST On-Off
- Neon Lamp: 110VAC

Note:

- RoHS Compliant

Illuminated Rocker Switches

103-7052-EV, 103-7053-EV

Available from Mouser Electronics

www.mouser.com 1-800-346-6873

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[103-7053-EV](#) [103-7052-EV](#)