



1095 HardBack Case



Interior dimensions:

40.1 x 28.3 x 5.2 cm (16" x 11" x 2")

Designed to protect 15" laptops

Watertight Gasket - Tight seal created when case is shut

The easy open latch remains shut under pressure or after impact

Automatic Purge Valve - Keeps water and dust out while balancing air pressure

Pick N Pluck™ with convoluted lid foam

Removable shoulder strap included

Legendary Guarantee of Excellence

Visit our

Watertight, crushproof, and dust proof



Black

1095 HardBack Case SPECIFICATIONS

Exterior Dimensions (L x W x D)		Interior Dimensions (L x W x D)			
43.6 x 33.6 x 6.6 cm (17" x 13" x 3")		40.1 x 28.3 x 5.2 cm (16" x 11" x 2")			
Lid Depth		Bottom Depth		Total Depth	
2.6 cm (1")		2.6 cm (1.03")		5.2 cm (2.06")	
Lid Depth		Bottom Depth		Total Depth	
2.6 cm (1.03")		2.6 cm (1.03")		5.2 cm (2.06")	
Weight w/Foam		Weight w/o Foam		Buoyancy Max.	
1.58 kg. (3.49 lbs)		1.38kg (3.05 lbs.)		0 kg (lbs.)	
Range Temperature					
-23 / 49° C (-10 / 120° F)					

Materials

Body	Latch	Lid O-Ring	Pins
ABS	ABS	EPDMStainless Steel	
Foam	Purge Body	Purge Vent	Purge O- Ring
	Polycarbonate	PTFE	70 Shore Nitrile

Configuration

Cat. #	Description
1095	1095 HardBack Case

1095 HardBack Case Accessories

No accessories are currently available for this product