


REV. DE



PT-01--24-01--22



SEE NOTE 15

PACKAGING VIEW LEAD STYLE SD -22

TABLE 2: SOCKET SPECIFICATION

LEAD STYLE	SERIES							NO OF FINGER CLIPS
	-1		F _I G	SL SDL	'B'	PIN LENGTH		
	SS	HSS					SD	
-1A	SC-1W1-XX-2 (SL & SDL N/R)	1	N/A	.038	.97	.553	14.05	4
-1B	SC-1W1-XX-1 (SL & SDL N/R)	1	N/A	.038	.97	.703	17.86	4
-1C	SC-1W1-XX-3 (SL & SDL N/R)	1	N/A	.038	.97	.453	11.51	4
-2	SC-1P1-XX (SL & SDL N/R)	1	N/A	.038	.97	.300	7.62	4
-3	SC-1S1-XX (SL & SDL N/R)	1	N/A	.038	.97	.203	5.16	4
-5	SC-2P1-XX (SS & HSS ONLY)	3	N/A	.038	.97	.703	17.86	4
-5A	SC-2P1-XX (SL & SDL N/R)	1	N/A	N/A	N/A	.703	17.86	4
-7	SC-1P3-XX (SL & SDL N/R)	1	N/A	N/A	N/A	.600	15.24	4
-8	SC-2P3-XX (SL & SDL N/R)	1	N/A	N/A	N/A	.542	13.77	4
-10	N/A	2	SC-3P1-XX	.038	.97	.230	5.84	4
-11	N/A	2	SC-4P1-XX	.028	.71	.240	6.10	4
-12	N/A	2	SC-5P1-XX	.028	.71	.190	4.83	4
-13	SC-2P7-XX (SS ONLY)	2	N/A	.039	.99	.310	7.87	4
-14	SC-1M1-XX (N/A)	1	N/A	N/A	N/A	.205	5.21	4
-15	SC-1M2-XX (N/A)	2	N/A	.028	.71	.167	4.24	4
-17	SC-7P1-XX (N/A)	1	N/A	N/A	N/A	.443	11.25	4
-18	SC-6P1-XX (SL & SDL N/R)	1	N/A	.038	.97	.353	8.97	4
-19	N/A	2	SC-8P1-XX	.016	.41	.165	4.19	4
-20	SC-9P1-XX (N/A)	2	N/A	.028	.71	.190	4.83	4
-21A	EZ-1W1-XX-2 (SL & SDL N/R)	1	N/A	N/A	N/A	.553	14.05	6
-21B	EZ-1W1-XX-1 (SL & SDL N/R)	1	N/A	N/A	N/A	.703	17.86	6
-21C	EZ-1W1-XX-3 (SL & SDL N/R)	1	N/A	N/A	N/A	.453	11.51	6
-22	EZ-1P1-XX (SL & SDL N/R)	1	N/A	.038	.96	.300	7.62	6
-23	EZ-1S1-XX (SL & SDL N/R)	1	N/A	N/A	N/A	.203	5.16	6
-28	EZ-2P3-XX (SL & SDL N/R)	1	N/A	N/A	N/A	.542	13.77	6
-29	EZ-2P2-XX (SL & SDL N/R)	1	N/A	N/A	N/A	.703	17.86	6
-30	EZ-3P1-XX (SL & SDL ONLY)	2	N/A	.038	.97	.230	5.84	6
-31	EZ-4P1-XX (SL & SDL ONLY)	2	N/A	.028	.71	.240	6.10	6
-32	EZ-5P1-XX (SL & SDL ONLY)	2	N/A	.028	.71	.190	4.83	6
-34	EZ-1M1-XX (N/A)	1	N/A	N/A	N/A	.205	5.21	6
-37	EZ-7P1-XX (N/A)	1	N/A	N/A	N/A	.443	11.25	6
-38	EZ-6P1-XX (SL & SDL N/R)	1	N/A	.038	.97	.353	8.97	6
-39	EZ-8P1-XX (SL & SDL ONLY)	2	N/A	.016	.41	.165	4.19	6
-40	EZ-9P1-XX (N/A)	2	N/A	.028	.71	.190	4.83	6
-41	SC-6P1-XX (N/A)	9	N/A	.005	.13	.353	8.97	4

SEE NOTE 13
SEE NOTE 14NOT AVAILABLE
IN -TT PLATING

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SANTER AND ITS AFFILIATES. IT IS
NOT TO BE REPRODUCED OR
TRANSMITTED IN ANY FORM OR BY
ANY MEANS, ELECTRONIC OR
MECHANICAL, INCLUDING
PHOTOCOPYING, RECORDING, OR
BY ANY INFORMATION STORAGE
AND RETRIEVAL SYSTEM, WITHOUT
WRITTEN CONSENT OF SANTER INC.


DELETED
FIGURE 7

FIGURE 9

DIMENSIONS ARE IN INCHES
UNLESS OTHERWISE NOTED
TOLERANCES ARE:
ONE PLACE DECIMALS ±.1[2.5] THREE PLACE DECIMALS ±.005 [.13]
TWO PLACE DECIMALS ±.01[.25] FOUR PLACE DECIMALS ±.002[.05]
ANGLES
± 2°


TITLE: ASSEMBLY
SOCKET STRIPDWG NO: XSX-1XX-XX-XX-X-X
SHEET 2 OF 2

FIGURE 1

(FOR -N OPTION, SEE NOTE 9 SHT.1)



FIGURE 2
(SEE NOTE 9 SHT.1)

FIGURE 3



OPTION -L: REPLACE BOTH END
POS. (BOTH ROWS) AS SHOWNFIGURE 4
(SEE NOTE 9 SHT.1)

FIGURE 8

OPTION -N
(FOR -SD STYLE, SEE NOTE 9 SHT.1)
(FOR HSS AND SS STYLES, SEE NOTES 3 & 4)
"B" DIMENSION FOR OPTION -N = NON FLUSH

santec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47151-1147
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY: MARK CHILTON 11-28-88

XSX-1XX-XX-XX-X-X
SHEET 2 OF 2