

60 Watt, 120v, 700°F 2-wire Soldering Iron with CT5A7 Tip



◀◀ previous print close next ▶▶

Product Details	
Catalog No.	W60P
UPC Code	037103474087
Type	Temperature Controlled
Wattage	100 W
Temperature Range	600° F / 700° F / 800° F
Cord Length	6 ft.
Components Supplied	CT5A7
Packaging	Industrial Box / Carton
Tech. Spec.	Solder Safety Warnings.pdf
Lineart	W60P.pdf
Low Res. Image	W60P_100.jpg
High Res. Image	W60P_300.jpg
Stock Item	Normal Stock Item

Package Details (Dimensions)

Email this Page

Product Features:

- Uses Weller "closed loop" method of controlling maximum tip temperature
- Portable line voltage iron - no base station required
- Stainless steel modular plug-in heater, greater efficiency & versatility
- Temperature is controlled by tip-600°F, 700°F, and 800°F tips available
- Nominal heat-up time with 700°F tip is 110 seconds
- Two-wire cord set
- Fume extraction adapter kit available - Cat. No. AKFE11
- Uses CT series tips
- Heating element type: Nichrome wound, plug in
- UL and cUL listed