



General ordering data

Order No.	9004240000
Part designation	H70,0/32
Version	Wire-end ferrule, 70 mm ²
EAN	4008190131395
Qty.	50 pc(s).

Technical data

Length	32 mm
Width	12.5 mm
Height	12.5 mm

Product data

Conductor rated cross-section	70 mm ²
AWG	2/0
Total length (L1)	32 mm
Contact surface diameter (D1)	12.5 mm
Metal sleeve thickness (S1)	0.35 mm

Approvals

Approvals institutes



Classifications

ETIM 2.0	EC000005
ETIM 3.0	EC000005
eClass 4.1	27-06-07-01
eClass 5.0	27-40-02-01
eClass 5.1	27-40-02-01

Similar products

Order No.	Part designation	Version
0282900000	H10,0/12	Wire-end ferrule, 10 mm ²
0124800000	H10,0/15	Wire-end ferrule, 10 mm ²
0379300000	H10,0/18	Wire-end ferrule, 10 mm ²
0492500000	H16,0/12	Wire-end ferrule, 16 mm ²
0124300000	H16,0/15	Wire-end ferrule, 16 mm ²
0375200000	H16,0/18	Wire-end ferrule, 16 mm ²
9004150000	H16,0/25	Wire-end ferrule, 16 mm ²
9004160000	H16,0/32	Wire-end ferrule, 16 mm ²

0124400000	H25,0/15	Wire-end ferrule, 25 mm ²
0375300000	H25,0/18	Wire-end ferrule, 25 mm ²
9004170000	H25,0/25	Wire-end ferrule, 25 mm ²
9004180000	H25,0/32	Wire-end ferrule, 25 mm ²
0368900000	H35,0/18	Wire-end ferrule, 35 mm ²
9004190000	H35,0/25	Wire-end ferrule, 35 mm ²
9451000000	H35,0/30S	Wire-end ferrule, 35 mm ²
9004200000	H35,0/32	Wire-end ferrule, 35 mm ²
9004210000	H50,0/18	Wire-end ferrule, 50 mm ²
9025880000	H50,0/25	Wire-end ferrule, 50 mm ²
9004220000	H50,0/32	Wire-end ferrule, 50 mm ²
9004230000	H70,0/25	Wire-end ferrule, 70 mm ²
9004250000	H95,0/25	Wire-end ferrule, 95 mm ²
9004260000	H95,0/32	Wire-end ferrule, 95 mm ²
9036240000	H120,0/32	Wire end ferrule, 120 mm ²
9036250000	H150,0/32	Wire end ferrule, 150 mm ²
9036260000	H185,0/32	Wire end ferrule, 185 mm ²