

Material	High Conductivity Seamless Copper Tube
Plating	Electro-Tin
Wire Size	500 STR/FLEX
Wire Type	Stranded Copper: Class G, H, I, K, M, Locomotive
Wire Strip Length	1-9/16 in.
Stud Size	1/2 in.
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
UL Temperature Rating	90° C
C.S.A Certified Wire Connector	Yes
Panduit Color Code on Barrel	PINK
Panduit Die Index No. on Barrel	P99
Alternate Industry Die Index No. () on Barrel	(L99)

LISTED
Wire Connector

								PANDUIT CORP. TINLEY PARK, ILLINOIS	
									LCAX500-12F-6
02	11/14	JHNU	JHNU	REVISED BENT TONGUE LENGTH: WAS 1.31	N10882JI-LCAX500-12F-CUST	RGB	RGB		Copper Lug - One-Hole, Standard Flex Barrel, 90° Angle Tongue
REV	DATE	BY	CHK	DESCRIPTION	ECN	-R	SUP	SCALE N/A	DRAWING NO / CAD FILE LCAX500-12F-CUST