


NOTES:

1. EACH SET SCREW IS THREADED INTO A HIGH TORQUE, BRASS INSERT DESIGNED TO PREVENT THREAD STRIPPING.
2. DECORATIVE SPUN ALUMINUM INLAY
3. PLASTIC OVERLAY MUST BE PRESENT ON TOP SURFACE.



TOLERANCES UNLESS NOTED			
.020-.157 [0.50-4.00]	± .004 [0.10]	SHAFT .251 [6.38]	+ .003 [0.07]
.158-.630 [4.01-16.00]	± .010 [0.25]	.126 [3.20]	- .000 [0.00]
.631-2.520 [16.03-64.00]	± .015 [0.38]	ANGULAR ±2 NON ACCUMULATIVE	

MODEL	COLOR	SHAFT DIA.	SET SCR.	"A"	"B"	"C"	"D"	"E"	"F"	"G"	"H"
PKG-40B	BLACK	.126 (3.20)	4-40	.437 (11.10)	.410 (10.41)	.304 (7.72)	.315 (8.00)	.079 (2.00)	.197 (5.00)	.385 (9.78)	.472 (11.99)
PKG-40R	RED	.126 (3.20)	4-40	.437 (11.10)	.387 (9.83)	.304 (7.72)	.315 (8.00)	.079 (2.00)	.197 (5.00)	.433 (11.00)	.472 (11.99)
PKG-50B	BLACK	.126 (3.20)	6-32	.551 (13.99)	.500 (12.70)	.422 (10.72)	.441 (11.20)	.056 (1.42)	.190 (4.83)	.395 (10.03)	.512 (13.00)
PKG-50B	BLACK	.251 (6.38)	6-32	.551 (13.99)	.500 (12.70)	.422 (10.72)	.441 (11.20)	.056 (1.42)	.190 (4.83)	.395 (10.03)	.512 (13.00)
PKG-50R	RED	.126 (3.20)	6-32	.551 (13.99)	.503 (12.77)	.422 (10.72)	.441 (11.20)	.079 (2.00)	.197 (5.00)	.422 (10.72)	.512 (13.00)
PKG-50R	RED	.251 (6.38)	6-32	.551 (13.99)	.503 (12.77)	.422 (10.72)	.441 (11.20)	.079 (2.00)	.197 (5.00)	.422 (10.72)	.512 (13.00)
PKG-60B	BLACK	.126 (3.20)	6-32	.660 (16.76)	.615 (15.62)	.512 (13.00)	.551 (13.99)	.080 (2.03)	.226 (5.74)	.430 (10.92)	.551 (13.99)
PKG-60B	BLACK	.251 (6.38)	6-32	.660 (16.76)	.615 (15.62)	.512 (13.00)	.551 (13.99)	.080 (2.03)	.226 (5.74)	.430 (10.92)	.551 (13.99)
PKG-60R	RED	.126 (3.20)	6-32	.673 (17.09)	.615 (15.62)	.512 (13.00)	.551 (13.99)	.122 (3.10)	.217 (5.51)	.461 (11.71)	.551 (13.99)
PKG-60R	RED	.251 (6.38)	6-32	.673 (17.09)	.615 (15.62)	.512 (13.00)	.551 (13.99)	.122 (3.10)	.217 (5.51)	.461 (11.71)	.551 (13.99)
PKG-70B	BLACK	.251 (6.38)	6-32	.740 (18.80)	.698 (17.73)	.591 (15.01)	.591 (15.01)	.080 (2.03)	.230 (5.84)	.453 (11.51)	.559 (14.20)
PKG-70B	BLACK	.126 (3.20)	6-32	.740 (18.80)	.698 (17.73)	.591 (15.01)	.591 (15.01)	.080 (2.03)	.230 (5.84)	.453 (11.51)	.559 (14.20)
PKG-70R	RED	.251 (6.38)	6-32	.740 (18.80)	.698 (17.73)	.591 (15.01)	.591 (15.01)	.122 (3.10)	.217 (5.51)	.453 (11.51)	.559 (14.20)

TOLERANCES UNLESS OTHERWISE NOTED.		INCH	DATE	DRAWING STATUS	REV.	A1	REVISED PER ECO-11-004820	RK	HMR
DECIMAL	METRIC	SEE CHART	8/88	☐ PRELIMINARY		A	RELEASED		
FRACTIONAL	ANGULAR	SEE CHART	9/89	☐ QUOTES					
THIRD ANGLE PROJECTION REFER TO ANSI Y14.5M-1982 FOR DWG. INTERPRETATION				☐ PROTOTYPE					
				☐ PRE-PRODUCTION					
				☐ RELEASE					
				DATA BASE: ECO2992					
				MATERIAL: MOLDED PHENOLIC RESIN					
				ALCO CONFIDENTIAL					
				This document contains information which is the exclusive property of Alco Electronics Products Inc. Distribution, reproduction or use by others is not permitted without the express written consent of Alco Electronics Products Inc.					
DO NOT SCALE DRAWING				TITLE: KNOB SERIES (PKG -40, -50, -60, -70)					
				SIZE: C		PROD. LINE		DWG. NO. 5-1437624-9	
								REV. A1	
				SCALE 4/1		SHEET 1 OF 1		CUSTOMER DRAWING	