



Item no.: 745-108
Product description: PCB TERMINAL STRIP 2 SOLDER PINS / POLE 8 POLE PIN
SPACING 5 MM / 0.197 IN WITHOUT FIXING FLANGE



Packing unit 60 pieces

Product group	4 (Printed Circuit)
Weight	16.317 g
Color	gray
No. of connection Points	8
No. of potentials	8
pole count	8
Height	19 mm
Height	0.748 in
Width	41.5 mm
Width	1.634 in
Depth	22.9 mm
Depth	0.902 in
Pin spacing from	5 mm
Pin spacing from	0.197 in
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	4 kV
Current intensity EN	32 A
Pollution degree	2
Measured voltage EN	630 V
Measured shock voltage	4 kV
Current intensity EN	32 A



Connection method	CAGE CLAMP® CONNECTION
Cross section [mm²]	0.08 - 4 mm²
Wiring method	solid
Cross section [mm²]	0.08 - 4 mm²
Cross section [mm²]	0.25 - 2.5 mm²
Cross section [mm²]	0.25 - 2.5 mm²
Cross section [AWG]	28 - 12 AWG
Strip length from	8 mm
Strip length to	9 mm
Material group	I
xxx-xxx/000-006	blue
xxx-xxx/000-009	light gray
xxx-xxx/000-016	green-yellow
xxx-xxx/000-017	light green
xxx-xxx/005-000	with fixing flange
xxx-xxx/005-xxx	with fixing flange



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm²]
745-108	CCA	NL5831	500	32	0,08-4
745-108	cURus	E45172	300/300	20/10	28-12
745-108	KEMA	2076500.01	500	32	0,08-4

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected