







NOTES:

1. THE UNSPECIFIED DIMENSIONS REFER TO SHEET 1.
2. PACKAGE SPECIFICATION FOR WITH FLANGE REFER TO PK-47151-002.

REVISE NOTE EC NO: S2014-0536 DRWN:FC00 CHKD:JTAN02 APPR:KHLIM		2013/12/05 2013/12/17 2013/12/20	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	
							MM ONLY		NTS	METRIC		
									TITLE			
L1		REV		QUALITY SYMBOLS			DRAWN BY DATE		1.0 HDMI RIGHT ANGLE HEADER ASSEMBLY(19 PIN) LEAD FREE			
							RZHANG 2004/07/20					
							CHECKED BY DATE		molex			
							GRMA 2004/07/20					
				QUALITY SYMBOLS			APPROVED BY DATE		SD-47151-001			
							YTYAP 2004/07/20					
							MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
							SEE SHEET 6				2 OF 8	
				QUALITY SYMBOLS	ANGULAR ± 3 °		SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A3					

10

9

8

7

6

5








4

3

2

1

WITH BACK COVER



NOTES:

1. THE UNSPECIFIED DIMENSIONS REFER TO 47151-0001.
2. PACKAGE SPECIFICATION FOR WITHOUT FLANGE REFER TO PK-47151-001.

REVISE NOTE EC NO: S2014-0536 2013/12/05 DRWN:FC500 CHKD:JTAN02 2013/12/17 APPR:KHLIM 2013/12/20		QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION		
					MM ONLY		NTS	METRIC			
DESCRIPTION	F _A =0		4 PLACES	± ---	± ---	DRAWN BY	DATE	THIS IS ONLY FOR 47151-1061/1071/1081			
	F _B =0		3 PLACES	± ---	± ---	RZHANG	2004/07/20	1.0 HDMI RIGHT ANGLE			
	F _C =0		2 PLACES	± 0.25	± ---	CHECKED BY	DATE	HEADER ASSEMBLY(19 PIN)			
			1 PLACE	± 0.25	± ---	GRMA	2004/07/20	LEAD FREE			
			0 PLACE	±	±	APPROVED BY	DATE	molex			
			ANGULAR ± 3 °		MATERIAL NO.		DOCUMENT NO.				
REV	L1		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE SHEET 6		SD-47151-001		3 OF 8		
					SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

9

8

7

6

5

4








3

2

1

10 9 8 7 6 5 4 3 2 1

WITH BACK COVER



THIS IS ONLY FOR
47151-1025/1075/1085/6022/6032/1026/2062

NOTES:

1. THE UNSPECIFIED DIMENSIONS REFER TO 47151-0002.
2. PACKAGE SPECIFICATION FOR WITH FLANGE:
OPTION 1: 47151-1026/2062/6032 REFER TO PK-47151-005,
OPTION 2: 47151-1102 REFER TO PK-47151-003,
OPTION 3: OTHER PART NUMBER REFER TO PK-47151-002.

REVISE NOTE		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
REV		DESCRIPTION				MM ONLY		NTS		METRIC			
L1		REV				DRAWN BY		DATE		TITLE			
						RZHANG		2004/07/20		1.0 HDMI RIGHT ANGLE			
						CHECKED BY		DATE		HEADER ASSEMBLY(19 PIN)			
						GRMA		2004/07/20		LEAD FREE			
						APPROVED BY		DATE		molex			
						YTYAP		2004/07/20		DOCUMENT NO.		SHEET NO.	
						MATERIAL NO.				SD-47151-001		4 OF 8	
						SEE SHEET 6							
						THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX							
						INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

10

9

8

7

6


5

4





3

2

1



WITHOUT TOP HOLE



NOTES:

1. THE UNSPECIFIED DIMENSIONS REFER TO 47151-1102.
2. PACKAGE SPECIFICATION FOR WITH FLANGE REFER TO PK-47151-002.

REV	DESCRIPTION	REVISE NOTE		
		EC NO:	DATE	BY
L1		S2014-0536	2013/12/05	DRWN:CS00
			2013/12/17	CHKD:JTAN02
			2013/12/20	APPR:KHLIM

QUALITY SYMBOLS
$\nabla_A = 0$
$\nabla_C = 0$
$\nabla_P = 0$

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	± 0.25	± 0.010
3 PLACES	± 0.25	± 0.010
2 PLACES	± 0.25	± 0.010
1 PLACE	± 0.25	± 0.010
0 PLACE	± 0.25	± 0.010
ANGULAR $\pm 3^\circ$		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE	
MM ONLY	
DRAWN BY	DATE
RZHANG	2004/07/20
CHECKED BY	DATE
GRMA	2004/07/20
APPROVED BY	DATE
YTYAP	2004/07/20
MATERIAL NO.	
SEE SHEET 6	

SCALE	DESIGN UNITS	THIRD ANGLE	
NTS	METRIC		PROJECTION
TITLE			
1.0 HDMI RIGHT ANGLE HEADER ASSEMBLY(19 PIN) LEAD FREE			
molex			
DOCUMENT NO.			SHEET NO.
SD-47151-001			5 OF 8
ALL INFORMATION THAT IS PROPRIETARY TO MOLEX SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

9

8

7

6

5

4

3

2

1

	10	9	8	7	6	5	4	3	2	1																																																																																																																																																																																																															
F	<table><tr><th rowspan="2">ASSEMBLY P/N</th><th colspan="5">DIMENSION</th><th colspan="4">FEATURE</th><th rowspan="2">HOUSING COLOUR</th><th rowspan="2">GOLD PLATING IN CONACT AREA</th><th rowspan="2">SHELL PLATING</th><th rowspan="2">REMARK</th></tr><tr><th>DIM A</th><th>DIM B</th><th>DIM C</th><th>DIM D</th><th>DIM E</th><th>FLANGE</th><th>BACK COVER</th><th>TOP HOLES</th><th>MYLAR</th></tr><tr><td>47151-0001</td><td rowspan="7">1.80</td><td rowspan="7">2.20</td><td rowspan="7">/</td><td rowspan="7">/</td><td rowspan="7">/</td><td rowspan="7">W/O</td><td rowspan="7">W/O</td><td rowspan="7">WITH</td><td rowspan="7">W/O</td><td>BLACK</td><td>SEE NOTE 2 (1)</td><td rowspan="7">SEE NOTE 2 (a)</td><td rowspan="14">FOR SHEET 1</td></tr><tr><td>47151-0041</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-0051</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-0011</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-0071</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-0061</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-0021</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-0031</td><td>NATURE</td><td>SEE NOTE 2 (1)</td><td rowspan="2">SEE NOTE 2 (b)</td></tr><tr><td>47151-0101</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-0141</td><td rowspan="7">1.45</td><td rowspan="7">1.45</td><td rowspan="7">/</td><td rowspan="7">/</td><td rowspan="7">/</td><td rowspan="7">W/O</td><td rowspan="7">W/O</td><td rowspan="7">WITH</td><td rowspan="7">W/O</td><td>BLACK</td><td>SEE NOTE 2 (2)</td><td rowspan="7">SEE NOTE 2 (a)</td></tr><tr><td>47151-0151</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-0111</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-0181</td><td>NATURE</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-0161</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-0121</td><td>BLACK</td><td>SEE NOTE 2 (1)</td><td rowspan="2">SEE NOTE 2 (b)</td></tr><tr><td>47151-0131</td><td>NATURE</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-0002</td><td rowspan="7">1.80</td><td rowspan="7">2.20</td><td rowspan="7">M3.0X0.5</td><td rowspan="7">16.08</td><td rowspan="7">13.38</td><td rowspan="7">WITH</td><td rowspan="7">W/O</td><td rowspan="7">WITH</td><td rowspan="7">W/O</td><td>BLACK</td><td>SEE NOTE 2 (1)</td><td rowspan="7">SEE NOTE 2 (a)</td><td rowspan="22">FOR SHEET 2</td></tr><tr><td>47151-0042</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-0062</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-0012</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-0052</td><td>NATURE</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-0072</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-0022</td><td>BLACK</td><td>SEE NOTE 2 (1)</td><td rowspan="2">SEE NOTE 2 (b)</td></tr><tr><td>47151-0032</td><td>NATURE</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-0102</td><td rowspan="7">1.45</td><td rowspan="7">1.45</td><td rowspan="7">M3.0X0.5</td><td rowspan="7">16.08</td><td rowspan="7">13.38</td><td rowspan="7">WITH</td><td rowspan="7">W/O</td><td rowspan="7">WITH</td><td rowspan="7">W/O</td><td>BLACK</td><td>SEE NOTE 2 (1)</td><td rowspan="7">SEE NOTE 2 (a)</td></tr><tr><td>47151-0142</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-0162</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-0112</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-0152</td><td>NATURE</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-0172</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-0122</td><td>BLACK</td><td>SEE NOTE 2 (1)</td><td rowspan="2">SEE NOTE 2 (b)</td></tr><tr><td>47151-0132</td><td>NATURE</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-6002</td><td rowspan="4">1.80</td><td rowspan="4">2.20</td><td rowspan="4">M3.0X0.5</td><td rowspan="4">14.25</td><td rowspan="4">11.28</td><td rowspan="4">WITH</td><td rowspan="4">W/O</td><td rowspan="4">WITH</td><td rowspan="4">W/O</td><td>BLACK</td><td>SEE NOTE 2 (1)</td><td rowspan="4">SEE NOTE 2 (a)</td><td rowspan="12">FOR SHEET 2</td></tr><tr><td>47151-6062</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-6082</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-6102</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-6172</td><td rowspan="4">1.45</td><td rowspan="4">1.45</td><td rowspan="4">M3.0X0.5</td><td rowspan="4">14.25</td><td rowspan="4">11.28</td><td rowspan="4">WITH</td><td rowspan="4">W/O</td><td rowspan="4">WITH</td><td rowspan="4">W/O</td><td>BLACK</td><td>SEE NOTE 2 (2)</td><td rowspan="4">SEE NOTE 2 (a)</td></tr><tr><td>47151-6162</td><td>SEE NOTE 2 (3)</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr></table>											ASSEMBLY P/N	DIMENSION					FEATURE				HOUSING COLOUR	GOLD PLATING IN CONACT AREA	SHELL PLATING	REMARK	DIM A	DIM B	DIM C	DIM D	DIM E	FLANGE	BACK COVER	TOP HOLES	MYLAR	47151-0001	1.80	2.20	/	/	/	W/O	W/O	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	FOR SHEET 1	47151-0041	SEE NOTE 2 (2)	47151-0051	SEE NOTE 2 (3)	47151-0011	SEE NOTE 2 (1)	47151-0071	SEE NOTE 2 (2)	47151-0061	SEE NOTE 2 (3)	47151-0021	SEE NOTE 2 (1)	47151-0031	NATURE	SEE NOTE 2 (1)	SEE NOTE 2 (b)	47151-0101	SEE NOTE 2 (1)	47151-0141	1.45	1.45	/	/	/	W/O	W/O	WITH	W/O	BLACK	SEE NOTE 2 (2)	SEE NOTE 2 (a)	47151-0151	SEE NOTE 2 (3)	47151-0111	SEE NOTE 2 (1)	47151-0181	NATURE	SEE NOTE 2 (2)	47151-0161	SEE NOTE 2 (3)	47151-0121	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (b)	47151-0131	NATURE	SEE NOTE 2 (1)	47151-0002	1.80	2.20	M3.0X0.5	16.08	13.38	WITH	W/O	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	FOR SHEET 2	47151-0042	SEE NOTE 2 (2)	47151-0062	SEE NOTE 2 (3)	47151-0012	SEE NOTE 2 (1)	47151-0052	NATURE	SEE NOTE 2 (2)	47151-0072	SEE NOTE 2 (3)	47151-0022	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (b)	47151-0032	NATURE	SEE NOTE 2 (1)	47151-0102	1.45	1.45	M3.0X0.5	16.08	13.38	WITH	W/O	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	47151-0142	SEE NOTE 2 (2)	47151-0162	SEE NOTE 2 (3)	47151-0112	SEE NOTE 2 (1)	47151-0152	NATURE	SEE NOTE 2 (2)	47151-0172	SEE NOTE 2 (3)	47151-0122	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (b)	47151-0132	NATURE	SEE NOTE 2 (1)	47151-6002	1.80	2.20	M3.0X0.5	14.25	11.28	WITH	W/O	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	FOR SHEET 2	47151-6062	SEE NOTE 2 (2)	47151-6082	SEE NOTE 2 (3)	47151-6102	SEE NOTE 2 (1)	47151-6172	1.45	1.45	M3.0X0.5	14.25	11.28	WITH	W/O	WITH	W/O	BLACK	SEE NOTE 2 (2)	SEE NOTE 2 (a)	47151-6162	SEE NOTE 2 (3)																								F
ASSEMBLY P/N	DIMENSION					FEATURE				HOUSING COLOUR	GOLD PLATING IN CONACT AREA		SHELL PLATING	REMARK																																																																																																																																																																																																											
	DIM A	DIM B	DIM C	DIM D	DIM E	FLANGE	BACK COVER	TOP HOLES	MYLAR																																																																																																																																																																																																																
47151-0001	1.80	2.20	/	/	/	W/O	W/O	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	FOR SHEET 1																																																																																																																																																																																																												
47151-0041										SEE NOTE 2 (2)																																																																																																																																																																																																															
47151-0051										SEE NOTE 2 (3)																																																																																																																																																																																																															
47151-0011										SEE NOTE 2 (1)																																																																																																																																																																																																															
47151-0071										SEE NOTE 2 (2)																																																																																																																																																																																																															
47151-0061										SEE NOTE 2 (3)																																																																																																																																																																																																															
47151-0021										SEE NOTE 2 (1)																																																																																																																																																																																																															
47151-0031	NATURE	SEE NOTE 2 (1)	SEE NOTE 2 (b)																																																																																																																																																																																																																						
47151-0101	SEE NOTE 2 (1)																																																																																																																																																																																																																								
47151-0141	1.45	1.45	/	/	/	W/O	W/O	WITH	W/O	BLACK	SEE NOTE 2 (2)	SEE NOTE 2 (a)																																																																																																																																																																																																													
47151-0151										SEE NOTE 2 (3)																																																																																																																																																																																																															
47151-0111										SEE NOTE 2 (1)																																																																																																																																																																																																															
47151-0181										NATURE	SEE NOTE 2 (2)																																																																																																																																																																																																														
47151-0161										SEE NOTE 2 (3)																																																																																																																																																																																																															
47151-0121										BLACK	SEE NOTE 2 (1)		SEE NOTE 2 (b)																																																																																																																																																																																																												
47151-0131										NATURE	SEE NOTE 2 (1)																																																																																																																																																																																																														
47151-0002	1.80	2.20	M3.0X0.5	16.08	13.38	WITH	W/O	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	FOR SHEET 2																																																																																																																																																																																																												
47151-0042										SEE NOTE 2 (2)																																																																																																																																																																																																															
47151-0062										SEE NOTE 2 (3)																																																																																																																																																																																																															
47151-0012										SEE NOTE 2 (1)																																																																																																																																																																																																															
47151-0052										NATURE	SEE NOTE 2 (2)																																																																																																																																																																																																														
47151-0072										SEE NOTE 2 (3)																																																																																																																																																																																																															
47151-0022										BLACK	SEE NOTE 2 (1)			SEE NOTE 2 (b)																																																																																																																																																																																																											
47151-0032	NATURE	SEE NOTE 2 (1)																																																																																																																																																																																																																							
47151-0102	1.45	1.45	M3.0X0.5	16.08	13.38	WITH	W/O	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)																																																																																																																																																																																																													
47151-0142										SEE NOTE 2 (2)																																																																																																																																																																																																															
47151-0162										SEE NOTE 2 (3)																																																																																																																																																																																																															
47151-0112										SEE NOTE 2 (1)																																																																																																																																																																																																															
47151-0152										NATURE	SEE NOTE 2 (2)																																																																																																																																																																																																														
47151-0172										SEE NOTE 2 (3)																																																																																																																																																																																																															
47151-0122										BLACK	SEE NOTE 2 (1)			SEE NOTE 2 (b)																																																																																																																																																																																																											
47151-0132	NATURE	SEE NOTE 2 (1)																																																																																																																																																																																																																							
47151-6002	1.80	2.20	M3.0X0.5	14.25	11.28	WITH	W/O	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)		FOR SHEET 2																																																																																																																																																																																																											
47151-6062										SEE NOTE 2 (2)																																																																																																																																																																																																															
47151-6082										SEE NOTE 2 (3)																																																																																																																																																																																																															
47151-6102										SEE NOTE 2 (1)																																																																																																																																																																																																															
47151-6172	1.45	1.45	M3.0X0.5	14.25	11.28	WITH	W/O	WITH	W/O	BLACK	SEE NOTE 2 (2)	SEE NOTE 2 (a)																																																																																																																																																																																																													
47151-6162										SEE NOTE 2 (3)																																																																																																																																																																																																															
E												E																																																																																																																																																																																																													
D												D																																																																																																																																																																																																													
C												C																																																																																																																																																																																																													
B												B																																																																																																																																																																																																													
A	<table><tr><td rowspan="10">REVISE NOTE EC NO: S2014-0536 2013/12/05 DRWN:FC00 CHKD:JTAN02 APPR:KHLIM 2013/12/20</td><td rowspan="10">QUALITY SYMBOLS F=0 F=0 F=0</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td rowspan="4">4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE</td><td rowspan="4">± --- ± --- ± 0.25 ± 0.25 ±</td><td rowspan="4">± --- ± --- ± --- ± --- ±</td><td>DRAWN BY</td><td>DATE</td><td rowspan="4">TITLE 1.0 HDMI RIGHT ANGLE HEADER ASSEMBLY(19 PIN) LEAD FREE molex</td><td rowspan="4">DOCUMENT NO. SD-47151-001</td><td rowspan="4">SHEET NO. 6 OF 8</td></tr><tr><td>RZHANG</td><td>2004/07/20</td></tr><tr><td>CHECKED BY</td><td>DATE</td></tr><tr><td>GRMA</td><td>2004/07/20</td></tr><tr><td colspan="2"></td><td>APPROVED BY</td><td>DATE</td><td colspan="4"></td></tr><tr><td colspan="2"></td><td>YTYAP</td><td>2004/07/20</td><td colspan="4"></td></tr><tr><td colspan="2"></td><td colspan="2">ANGULAR ± 3 °</td><td colspan="2">MATERIAL NO.</td><td colspan="4"></td></tr><tr><td colspan="2"></td><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">SEE SHEET 6</td><td colspan="4"></td></tr><tr><td colspan="2"></td><td colspan="2"></td><td>SIZE A3</td><td colspan="5">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>											REVISE NOTE EC NO: S2014-0536 2013/12/05 DRWN:FC00 CHKD:JTAN02 APPR:KHLIM 2013/12/20	QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE	± --- ± --- ± 0.25 ± 0.25 ±	± --- ± --- ± --- ± --- ±	DRAWN BY	DATE	TITLE 1.0 HDMI RIGHT ANGLE HEADER ASSEMBLY(19 PIN) LEAD FREE molex	DOCUMENT NO. SD-47151-001	SHEET NO. 6 OF 8	RZHANG	2004/07/20	CHECKED BY	DATE	GRMA	2004/07/20			APPROVED BY	DATE							YTYAP	2004/07/20							ANGULAR ± 3 °		MATERIAL NO.								DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE SHEET 6										SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					A																																																																																																																																							
REVISE NOTE EC NO: S2014-0536 2013/12/05 DRWN:FC00 CHKD:JTAN02 APPR:KHLIM 2013/12/20	QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																																																																																																																																																																																	
		4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE	± --- ± --- ± 0.25 ± 0.25 ±	± --- ± --- ± --- ± --- ±	DRAWN BY	DATE	TITLE 1.0 HDMI RIGHT ANGLE HEADER ASSEMBLY(19 PIN) LEAD FREE molex	DOCUMENT NO. SD-47151-001	SHEET NO. 6 OF 8																																																																																																																																																																																																																
					RZHANG	2004/07/20																																																																																																																																																																																																																			
					CHECKED BY	DATE																																																																																																																																																																																																																			
					GRMA	2004/07/20																																																																																																																																																																																																																			
				APPROVED BY	DATE																																																																																																																																																																																																																				
				YTYAP	2004/07/20																																																																																																																																																																																																																				
				ANGULAR ± 3 °		MATERIAL NO.																																																																																																																																																																																																																			
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE SHEET 6																																																																																																																																																																																																																			
						SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																																																																																																																																																		
	10	9	8	7	6	5	4	3	2	1																																																																																																																																																																																																															

F

E

D

C

B

A

F

E

D

C

B

A

ASSEMBLY P/N	DIMENSION					FEATURE				HOUSING COLOUR	GOLD PLATING IN CONACT AREA	SHELL PLATING	REMARK
	DIM A	DIM B	DIM C	DIM D	DIM E	FLANGE	BACK COVER	TOP HOLES	MYLAR				
47151-1001	1.80	2.20	/	/	/	W/O	WITH	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	FOR SHEET 3
47151-1041											SEE NOTE 2 (2)		
47151-1051											SEE NOTE 2 (3)		
47151-1003											SEE NOTE 2 (4)		
47151-1061									WITH	BLACK	SEE NOTE 2 (1)		
47151-1071											SEE NOTE 2 (2)		
47151-1081											SEE NOTE 2 (3)		
47151-1011											SEE NOTE 2 (1)		
47151-1211									W/O	NATURE	SEE NOTE 2 (2)		
47151-1311											SEE NOTE 2 (3)		
47151-1021											SEE NOTE 2 (1)		
47151-1091											SEE NOTE 2 (3)		
47151-1031											SEE NOTE 2 (1)		
47151-1101	1.45	1.45	/	/	/	W/O	WITH	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	
47151-1141											SEE NOTE 2 (2)		
47151-1151											SEE NOTE 2 (3)		
47151-1111											SEE NOTE 2 (1)		
47151-1161										NATURE	SEE NOTE 2 (2)		
47151-1171											SEE NOTE 2 (3)		
47151-1121											SEE NOTE 2 (1)		
47151-1131											SEE NOTE 2 (1)		
47151-7102	1.45	1.45	M3.0x0.5	16.08	13.38	WITH	WITH	W/O	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	FOR SHEET 5
47151-7142											SEE NOTE 2 (2)		
47151-7162											SEE NOTE 2 (3)		

REVISE NOTE

EC NO: S2014-0536

2013/12/05

DRWN:FC500

2013/12/17

CHKD:JTAN02

2013/12/20

APPR:KHLIM

2013/12/20

DESCRIPTION

REV

L1

QUALITY SYMBOLS

$\nabla_A=0$

$\nabla_G=0$

$\nabla_P=0$

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± 0.25	± ---
1 PLACE	± 0.25	± ---
0 PLACE	±	±

ANGULAR ± 3 °

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE

MM ONLY

DRAWN BY	DATE
RZHANG	2004/07/20
CHECKED BY	DATE
GRMA	2004/07/20
APPROVED BY	DATE
YTYAP	2004/07/20

MATERIAL NO.

SEE SHEET 6

SIZE

A3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SCALE

NTS

DESIGN UNITS

METRIC

THIRD ANGLE PROJECTION

TITLE

1.0 HDMI RIGHT ANGLE
HEADER ASSEMBLY(19 PIN)
LEAD FREE

molex

DOCUMENT NO.

SD-47151-001

SHEET NO.

7 OF 8

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[47151-1021](#)