

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

84729-0001

Status:

Active

Overview:

Industrial USB Plugs and Receptacles

Description:

USB Type A Panel Mount Receptacle 5/C Pigtail 0.152m Length, 28 AWG

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable Assemblies
Series	84729
Comments	Fully shielded for EMI/RFI protection
Connector to Connector	Type A Recept-to-Type A Plug
MolexKits	Yes
Overview	Industrial USB Plugs and Receptacles
Product Name	Industrial USB
UPC	822348842155

Physical	
Cable Length	0.152m
Circuits (Loaded)	4
Color - Resin	Black
Gender	Receptacle
Lock to Mating Part	None
Material - Resin	Nylon, Polyester
Net Weight	12.622/g
Packaging Type	Bag
Single Ended	Yes
Termination Interface: Style	N/A
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP67, NEMA 6P
Wire Insulation Diameter	N/A
Wire Size AWG	N/A
Wire/Cable Type	USB

Electrical	
Current - Maximum per Contact	1A
Shield Type	N/A
Shielded	No
Voltage - Maximum	30V AC (RMS)

Material Info

Reference - Drawing Numbers	
Sales Drawing	SD-84729-005



Series
image - Reference only

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

84729Series

Mates With

84727 USB Type A Plug to Shielded Pigtail Receptacles

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION