

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
 FREEPORT, ALABAMA
 FED. MFR. CODE 91929

SWITCH - ENCLOSED

CATALOG LISTING
BAF1-3CN18X1

ISSUE 1

M BAF1-3CN18X1

DRAWING NUMBER

7

2

ISSUE

3

REPLACES

RELEASE NO. SR-13006

CHECK

REVISIONS

| | | | |
|---|------------|-------|-------------|
| A | SR-13006 | REN | 21 SEP 67 |
| B | CO 40076-C | T M M | 12 JAN 82 |
| C | CO51000-E | K A G | 25 AUG 83 |
| D | CO-54987F | J A S | 14 MARCH 85 |
| E | CO 72788 | C O | 22 AUG 92 |
| F | H 77179-E | P A T | 17 MAY 94 |

CHECK

6

OCT 67

67

SEP 67

SEP 67

SEP 67

SEP 67


SEP 67

SEP 67

SEP 67

SEP 67

SEP 67



NOTE -

1-6-32UNC X.219REF BINDING HEAD TERMINAL SCREWS (STAKED)

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

| CHARACTERISTICS | ELECTRICAL DATA | SCALE FULL |
|--|---|---|
| OPERATING POSITION - - - - - 15° MAX | CONTACT ARRANGEMENT S P D T MAINTAINED CONTACT | DO NOT SCALE PRINT |
| RESET CHARACTERISTICS | -L19- 15 A-125, 250, OR 480 VAC 3/4 HP-125 VAC; 1 1/2 HP-250 VAC 1/2 A-125 VDC; 1/4 A-250 VDC | UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: |
| OPERATING FORCE - - - - - 1 1/2 LB MAX | | ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.008 ANGLES ± |
| OVERTRAVEL - - - - - .219 MIN | | WEIGHT |
| SWITCH-BASIC REPLACEMENT - - BA-3CX71B | | |

