


PRODUCT NO.
SEE TABLE



NOTES:

- 1 MADE IN ACCORDANCE WITH PRODUCT SPEC. BUS-12-001.
- 2 COLOR TO BE LIGHT BLUE WITH DARK BLUE TRACER ON EDGE OF FIRST POSITION ONLY
- 3 UL LISTED STYLE 2651. CSA CERTIFIED PER C22.2 (LATEST REVISION).

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE			
ltr	ecn no	dr	date	tolerances unless otherwise specified						title			
A	—	TB	11/28/84	angles	linear	.XX±.01/.3				INCH/MM	#28 AWG SOLID DOUBLE SCALLOPED PVC RD. COND. CABLE		
B	V82043	RGD	11/13/98			.XXX±.005/.13							
C	M06-0282	MHT	7/26/06			0'±2'	.XXXX±.0020/.05					scale 1:1	
				dr	—	11/28/84			dwg no	sheet 1 of 2			size
				enrg	R.DOUTRICH	11/28/84							
				chr	R.DOUTRICH	11/28/84							
				appd	R.DOUTRICH	11/28/84							
sheet index		revision sheet		C	C								
				1	2								



PRODUCT NO.
77060-XXX

77060-XXX

NO. OF CONDUCTORS
(MIN. 9, MAX 64)
LENGTH

TOLERANCE FOR DIMS		
NO. OF CONDUCTORS	DIM. A±	DIM. B±
9 THRU 15	.007/-.18	.010/-.25
16 THRU 37	.009/-.23	.015/-.38
38 THRU 64	.011/-.28	.015/-.38

X	MIN. LENGTH FT/M
0	100/30.48
1	100/30.48
3	300/91.44
4	300/91.44

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE			
ltr	ecn	no	dr	date		tolerances unless otherwise specified				title			
C						angles		linear		.XX±.01/.3		INCH/MM	
						0'±2'				.xxx±.005/.13			
										xxxx±.0020/.051		scale 1:1	
						dr		-		11/28/84		FCJ	
						enr		R.DOUTRICH		11/28/84		dwg no	
						chr		R.DOUTRICH		11/28/84		sheet2 of 2 size	
						app		R.DOUTRICH		11/28/84		A3	
sheet index		revision sheet										type Product Customer Drawing	

form: A3