



Date: 31/03/2003
Page: 1 of 2



Detail "A" Plug



PART NUMBERS: 110-178 0.5M 4 POLE SVHS CABLE

110-024 1M 4 POLE SVHS CABLE
110-025 3M 4 POLE SVHS CABLE
110-026 5M 4 POLE SVHS CABLE
110-027 10M 4 POLE SVHS CABLE
110-179 15M 4 POLE SVHS CABLE
110-180 20M 4 POLE SVHS CABLE

110-178 to 110-180
110-181 to 110-185
110-024 to 110-027

Date: 31/03/2003
Page: 2 of 2

TECHNICAL SPECIFICATION

PART NUMBERS: 110-178 0.5M 4 POLE SVHS CABLE

110-024 1M 4 POLE SVHS CABLE

110-025 3M 4 POLE SVHS CABLE

110-026 5M 4 POLE SVHS CABLE

110-027 10M 4 POLE SVHS CABLE

110-179 15M 4 POLE SVHS CABLE

110-180 20M 4 POLE SVHS CABLE

LOW-LOSS TWIN 75ohm OFC COAXIAL CABLE,
4 POLE GOLD PLATED S VIDEO CONNECTOR PLUG to PLUG

SPECIFICATION

OFC OFC

[(16/0.10mm x1C+80/0.10mm)x2C]x1C

CONSTRUCTION

		FIRST SHIELD	MATERIAL: DIAMETER:	OFC Braid	2.25mm
CONDUCTOR	MATERIAL: 0.078mm SIZE: 10/0.10mm STRANDING: 0.37mm DIAMETER:	INNER JACKET	MATERIAL: DIAMETER:	PVC	2.8mm
INSULATION	MATERIAL: PEF DIAMETER: 1.85mm	SECOND SHIELD	MATERIAL: DIAMETER:		
JACKET	MATERIAL: PVC DIAMETER: 7.2mm	COLOUR: MAROON			

