

(0,80 mm) .0315"

CLE SERIES

COST EFFECTIVE MICRO SOCKET

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?CLE

Insulator Material:

Black Liquid Crystal Polymer

Contact Material:

BeCu

Plating:

Au over 50µ" (1,27 µm) Ni

Current Rating (CLE/FTE):

2.7 A per pin

(1 pin powered per row)

Operating Temp Range:

-55°C to +125°C

Contact Resistance:

15 mΩ

Insertion Depth:

Top Entry = (1,73 mm) .068"

to (3,18 mm) .125" with

(0,38 mm) .015" wipe, or

pass-through

Bottom Entry = (3,23 mm) .127"

minimum plus

board thickness

Insertion Force:

(Single contact only)

2.0 oz (0,56 N)

Normal Force:

75 grams (0,73 N)

Withdrawal Force:

(Single contact only)

1.2 oz (0,33 N)

Max Cycles:

100 with 10µ" (0,25 µm) Au

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0,10 mm) .004" max (04-65)







(0,15 mm) .006" max (66-90)

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



Mates with:
FTE, AW



TAPE & REEL AVAILABILITY

No tooling charges.
Minimum order is the lesser of a full reel quantity or 125 pieces. Order any quantity above minimum. In-house design, manufacture. Quick turn-around.
Call Samtec for specifications and ordering information.

Note: Some lengths, styles and options are non-standard, non-returnable.