

NT14B PF

DESCRIPTION

- Blue disposable 100% Nitrile glove.
- Ambidextrous glove.
- Powder free glove.
- 4 available sizes : 6.5, 7.5, 8.5 and 9.
- Box of 50 gloves.

CHARACTERISTICS

- Nitrile formulation for low hand fatigue.
- Beaded cuff for a better tearing resistance.
- Textured finish, light and resistant.
- 21CFR (USA) and European Directives compliant for food contact.
- Length : 350 mm approximately.
- Double wall thickness : 0,22 mm approximately.

PERFORMANCES

- Good resistance to puncture.
- Flexible and comfortable offering excellent dexterity.
- Beaded cuff for an easy donning and offering good tear resistance.
- In compliance with the standards EN420 (General requirements), EN388 (Mechanical Hazards) and EN374 (Chemical and Micro-organisms Hazards) by the notified laboratory BSI.
- Manufactured under EC quality assurance system carried out by the BSI body.

APPLICATIONS

- Handlings of slightly aggressive products, recommended only for short contacts.
- Sectors of activity : Food handling and processing, painting, electronics, laboratory handlings.



This glove is certified to comply with the essential requirements of European Directive EEC/89/686 of December 21st, 1989 relative to personal protective equipment submitted to CE type examination issued by a notified laboratory, who certifies the conformity of this glove with the EN standards to which it responds and certifies the performance levels obtained during tests, and manufactured under a CE quality assurance system carried out by a notified body.

CE 0086



EN 420

EN 420

5 Dexterity

EN 388

2 Abrasion

0 Cut

0 Tear

0 Puncture



EN 388

Mechanical hazards



EN 374

Chemical hazards



EN 421

Radioactive contamination

Order codes

Sizes	6.5 (S)	7.5 (M)	8.5 (L)	9 (XL)
NT14B PF	9999188	9999189	9999190	9999191