

ADDA USA

DC FAN SPECIFICATIONS

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
45 X 45 X 6	AD4505LX-K90	HYPRO	5	0.10	0.50	4300	6.2	0.056	23.0	24	0	CE	560	19.30
45 X 45 X 6	AD4505MX-K90	HYPRO	5	0.12	0.60	5000	7.1	0.074	25.5	24	0,6	CE	560	19.30
45 X 45 X 6	AD4505HX-K90	HYPRO	5	0.14	0.70	6000	9.2	0.103	32.6	24	0,6	CE	560	19.30
45 X 45 X 6	AD4505LB-K90(S)	1B & 1S	5	0.10	0.50	4500	6.5	0.059	23.3	24	0,6	CE	560	19.30
45 X 45 X 6	AD4505MB-K90(S)	1B & 1S	5	0.12	0.60	5500	7.2	0.085	26.5	24	0,6	CE	560	19.30
45 X 45 X 6	AD4505HB-K90(S)	1B & 1S	5	0.14	0.70	6200	9.5	0.111	33.0	24	0,6	CE	560	19.30
45 X 45 X 6	AD4512LX-K90	HYPRO	12	0.08	0.96	4300	6.2	0.056	23.0	24	0,6	CE	560	19.30
45 X 45 X 6	AD4512MX-K90	HYPRO	12	0.09	1.08	5000	7.1	0.074	25.5	24	0,6	CE	560	19.30
45 X 45 X 6	AD4512HX-K90	HYPRO	12	0.10	1.20	6000	9.2	0.103	32.6	24	0,6	CE	560	19.30
45 X 45 X 6	AD4512LB-K90(S)	1B & 1S	12	0.08	0.96	4500	6.5	0.059	23.3	24	0,6	CE	560	19.30
45 X 45 X 6	AD4512MB-K90(S)	1B & 1S	12	0.09	1.08	5500	7.2	0.085	26.5	24	0	CE	560	19.30
45 X 45 X 6	AD4512HB-K90(S)	1B & 1S	12	0.10	1.20	6200	9.5	0.111	33.0	24	0,6	CE	560	19.30
45 X 45 X 7	AD4505MX-QA0	HYPRO	5	0.09	0.45	5000	1.6	0.224	25.5	23	0	CE	480	
45 X 45 X 7	AD4505HX-QA0	HYPRO	5	0.14	0.70	5700	1.8	0.332	28.5	23	0,6	CE	480	
45 X 45 X 7	AD4505HX-QA3	HYPRO	5	0.12	0.60	6200	2.1	0.397	31.2	23	3	CE	480	
45 X 45 X 7	AD4505HB-QA3	BALL	5	0.12	0.60	6200	2.1	0.397	31.2	23	3	CE	480	
45 X 45 X 9	AD4505HX-RB3	HYPRO	5	0.22	1.10	4500	3.1	0.213	31.8	26	3	CE	500	
45 X 45 X 10	AD4505LX-G70(T)	HYPRO	5	0.16	0.80	3800	6.8	0.062	17.5	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4505MX-G70	HYPRO	5	0.10	0.50	4200	6.9	0.069	21.6	24	0,6	CE	500	24.64
45 X 45 X 10	AD4505MX-G70(T)	HYPRO	5	0.18	0.90	4500	7.5	0.078	22.0	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4505MX-GD0	HYPRO	5	0.25	1.25	4200	2.0	0.290	22.0	26	0,6	CE	500	24.64
45 X 45 X 10	AD4505MX-GD1	HYPRO	5	0.15	0.75	5000	2.3	0.342	31.1	26	1	CE	500	24.64
45 X 45 X 10	AD4505HX-G70	HYPRO	5	0.20	1.00	5500	9.1	0.107	27.4	24	0	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4505HX-G76	HYPRO	5	0.20	1.00	5500	9.1	0.109	28.6	24	6	CE	500	24.64
45 X 45 X 10	AD4505HX-GD0	HYPRO	5	0.22	1.10	5200	2.7	0.434	27.4	26	0,3	CE	500	24.64
45 X 45 X 10	AD4505HX-GD1	HYPRO	5	0.17	0.85	4800	7.0	0.050	28.9	26	1	CE	500	24.64
45 X 45 X 10	AD4505LB-G70	BALL	5	0.16	0.80	4200	7.0	0.066	20.4	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4505MB-G70	BALL	5	0.16	0.80	4200	6.9	0.069	21.6	24	0	CE	500	24.64
45 X 45 X 10	AD4505MB-G76	BALL	5	0.18	0.90	4500	7.5	0.078	22.0	24	6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4505MB-GD0	BALL	5	0.25	1.25	4200	2.0	0.290	22.0	26	0,6	CE	500	24.64
45 X 45 X 10	AD4505HB-G70	BALL	5	0.20	1.00	5000	8.2	0.101	26.2	24	0	CE	500	24.64
45 X 45 X 10	AD4505HB-G70(S)	1B & 1S	5	0.20	1.00	5500	9.8	0.116	27.5	24	0	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4505HB-G70(T)	BALL	5	0.20	1.00	5500	9.1	0.107	27.4	24	0,6	CE	500	24.64
45 X 45 X 10	AD4505HB-GD0	BALL	5	0.22	1.10	5200	2.7	0.434	35.3	26	0,6	CE	500	24.64
45 X 45 X 10	AD4505LS-G70(T)	S	5	0.16	0.80	3800	6.8	0.062	17.5	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4505MS-G70	S	5	0.16	0.80	4200	6.9	0.069	21.6	24	0	CE	500	24.64
45 X 45 X 10	AD4505MS-G76	S	5	0.18	0.90	4500	7.5	0.078	22.0	24	6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4505HS-G70	S	5	0.20	1.00	5500	9.1	0.107	27.4	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4505HS-GD0(Y)	S	5	0.22	1.10	5200	2.7	0.434	35.3	26	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512LX-G70(T)	HYPRO	12	0.06	0.72	3800	6.8	0.062	17.5	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512MX-G70	HYPRO	12	0.07	0.84	4200	6.9	0.069	21.6	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512MX-G70(T)	HYPRO	12	0.07	0.84	4500	7.5	0.078	22.0	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512HX-G70	HYPRO	12	0.09	1.08	6500	10.4	0.145	31.6	24	0,6	UL,CUL,TUV,CE	500	24.64

NOTE B=Ball S=Sleeve X= Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

ADDA USA

DC FAN SPECIFICATIONS

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
45 X 45 X 10	AD4512HX-G70(T)	HYPRO	12	0.09	1.08	5500	9.1	0.107	27.4	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512LB-G70	BALL	12	0.06	0.72	4200	7.0	0.066	20.4	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512MB-G70	Bor1B1S	12	0.07	0.84	4200	6.9	0.069	21.6	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512MB-G70(T)	BALL	12	0.07	0.84	4500	7.5	0.078	22.0	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512MB-G72(S)	1B & 1S	12	0.08	0.96	4800	7.9	0.081	23.7	24	2	CE	500	24.64
45 X 45 X 10	AD4512HB-G70	Bor1B1S	12	0.09	1.08	5000	8.3	0.097	26.1	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512HB-G70(T)	BALL	12	0.09	1.08	5500	9.1	0.107	27.4	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512LS-G70(T)	S	12	0.06	0.72	3800	6.8	0.062	17.5	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512MS-G70	S	12	0.07	0.84	4200	6.9	0.069	21.6	24	0	CE	500	24.64
45 X 45 X 10	AD4512MS-G76	S	12	0.07	0.84	4200	6.9	0.069	21.6	24	6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512MS-G70(T)	S	12	0.07	0.84	4500	7.5	0.078	22.0	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512HS-G70	S	12	0.09	1.08	5000	8.3	0.097	26.1	24	0	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512HS-G70(T)	S	12	0.09	1.08	5500	9.1	0.109	28.6	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4524LX-G70(T)	HYPRO	24	0.06	1.44	3800	6.8	0.062	17.5	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4524MX-G70(T)	HYPRO	24	0.07	1.68	4800	7.5	0.078	22.0	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4524HX-G70(T)	HYPRO	24	0.08	1.92	5500	9.1	0.109	28.6	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4524LB-G70(T)	BALL	24	0.06	1.44	3800	6.8	0.062	17.5	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4524LB-G70(S)	BALL	24	0.06	1.44	4200	7.0	0.066	20.4	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4524MB-G70(T)	BALL	24	0.09	2.16	4500	7.5	0.078	22.0	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4524MB-G70(S)	BALL	24	0.07	1.68	4800	7.9	0.081	23.7	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4524HB-G70(T)	BALL	24	0.08	1.92	5500	9.1	0.109	28.6	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4524LS-G70(T)	BALL	24	0.06	1.44	3800	6.8	0.062	17.5	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4524MS-G70(T)	BALL	24	0.07	1.68	4800	7.5	0.078	22.0	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4524HS-G70(T)	BALL	24	0.08	1.92	5500	9.1	0.109	28.6	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4524HB-G70(S)	BALL	24	0.08	1.92	5700	9.8	0.107	27.4	24	0,6	UL,CUL,TUV,CE	500	24.64
50 X 50 X 15	AD5005MS-D70	S	5	0.24	1.20	4300	12.6	0.113	29.0	55	0	CE		
50 X 50 X 15	AD5012LX-D70	HYPRO	12	0.08	0.96	3600	10.8	0.084	23.6	55	0	CE		
50 X 50 X 15	AD5012MX-D70	HYPRO	12	0.10	1.20	4300	12.6	0.113	29.0	55	0	CE		
50 X 50 X 15	AD5012HX-D70	HYPRO	12	0.14	1.68	4800	14.4	0.141	30.7	55	0,6	CE		
50 X 50 X 15	AD5012UX-D76	HYPRO	12	0.20	2.40	5500	16.5	0.181	33.8	55	6	CE		
50 X 50 X 15	AD5012LB-D70	BALL	12	0.08	0.96	3600	10.8	0.084	23.6	55	0,6	CE		
50 X 50 X 15	AD5012MB-D70	BALL	12	0.10	1.20	4300	12.6	0.113	29.0	55	0,6	CE		
50 X 50 X 15	AD5012MB-D76(S)	1B & 1S	12	0.10	1.20	4500	13.4	0.126	28.5	55	6	CE		
50 X 50 X 15	AD5012HB-D70	BALL	12	0.14	1.68	4800	14.4	0.141	30.7	55	0,6	CE		
50 X 50 X 15	AD5012HB-D70(S)	1B & 1S	12	0.14	1.68	500	15.0	0.152	31.4	55	0,6	CE		
50 X 50 X 15	AD5012UB-D70	BALL	12	0.20	2.40	5500	16.5	0.181	33.8	55	0,6	CE		
50 X 50 X 15	AD5012UB-D70(S)	1B & 1S	12	0.20	2.40	5700	17.1	0.194	34.5	55	0,6	CE		
50 X 50 X 15	AD5012LS-D70	S	12	0.08	0.96	3600	10.8	0.084	23.6	55	0	CE		
50 X 50 X 15	AD5012MS-D70	S	12	0.10	1.20	4300	12.6	0.113	29.0	55	0,6	CE		
50 X 50 X 15	AD5012HS-D76	S	12	0.14	1.68	4800	14.4	0.141	30.7	55	6	CE		
50 X 50 X 15	AD5012US-D76	S	12	0.20	2.40	5500	16.5	0.181	33.8	55	6	CE		
52 X 52 X 9	AD0505MX-RB1	HYPRO	5	0.17	0.85	4800	3.0	0.320	34.0	28	0,3	CE		
52 X 52 X 9	AD0505HX-RB0	HYPRO	5	0.22	1.10	5000	3.2	0.320	34.0	28	0,3	CE		

NOTE B=Ball S=Sleeve X= Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

ADDA USA

DC FAN SPECIFICATIONS

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
52 X 52 X 9	AD0505HX-RB1	HYPRO	5	0.22	1.10	5000	9.5	0.100	31.7	28	1	CE		
52 X 52 X 9	AD0505MB-RB1	BALL	5	0.17	0.85	4800	3.0	0.320	34.0	28	1	CE		
52 X 52 X 9	AD0512MX-RB0	HYPRO	12	0.10	1.20	4800	3.0	0.320	34.0	28	0	CE		
50 X 50 X 10	AD0505LX-G70(T)	HYPRO	5	0.12	0.60	3700	9.0	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0505MX-G70	HYPRO	5	0.18	0.90	4300	10.5	0.100	24.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0505MX-G90	HYPRO	5	0.12	0.60	3300	8.5	0.068	24.9	24	0	UL,CUL,CE		
50 X 50 X 10	AD0505HX-G70(T)	HYPRO	5	0.23	1.15	5000	11.2	0.130	26.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0505HX-G90	HYPRO	5	0.15	0.75	3800	9.8	0.082	28.6	50	0	UL,CUL,CE		
50 X 50 X 10	AD0505LB-G70(T)	BALL	5	0.12	0.60	3700	9.0	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0505LB-G70(TS)	1B & 1S	5	0.12	0.60	3900	9.4	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0505MB-G70	BALL	5	0.14	0.70	4600	10.5	0.100	24.0	18	0	CE		
50 X 50 X 10	AD0505MB-G70(T)	BALL	5	0.18	0.90	4300	10.5	0.100	24.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0505MB-G70(TS)	1B & 1S	5	0.18	0.90	4500	10.8	0.100	25.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0505HB-G70(T)	BALL	5	0.23	1.15	5000	11.2	0.130	26.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0505HB-G90	BALL	5	0.15	0.75	3800	9.8	0.082	28.6	24	0	UL,CUL,CE		
50 X 50 X 10	AD0505HB-G96	BALL	5	0.15	0.75	3800	9.8	0.082	28.6	24	6	CE		
50 X 50 X 10	AD0505LS-G70	S	5	0.12	0.60	3700	9.0	0.060	20.0	18	0	TUV,CE		
50 X 50 X 10	AD0505LS-G76	S	5	0.12	0.60	3700	9.0	0.060	20.0	18	0	UL,CUL,TUV,CE		
50 X 50 X 10	AD0505MS-G70(T)	S	5	0.18	0.90	4300	10.5	0.100	24.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0505MS-G90	S	5	0.12	0.60	3300	8.5	0.068	24.9	24	0	UL,CUL,CE		
50 X 50 X 10	AD0505HS-G70	S	5	0.18	0.90	5200	11.9	0.130	28.0	18	0	UL,CUL,TUV,CE		
50 X 50 X 10	AD0505HS-G70(T)	S	5	0.23	1.15	500	11.2	0.130	26.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0512LX-G70(T)	HYPRO	12	0.10	0.72	3700	9.0	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0512MX-G70(T)	HYPRO	12	0.07	0.84	4300	10.5	0.100	24.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0512MX-G72	HYPRO	12	0.10	1.20	4300	10.5	0.100	24.0	18	2	CE		
50 X 50 X 10	AD0512MX-G90	HYPRO	12	0.07	0.84	3300	8.5	0.068	24.9	50	0	UL,CUL,CE		
50 X 50 X 10	AD0512HX-G70	HYPRO	12	0.09	1.08	5000	11.2	0.130	26.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0512HX-G76(UT)	HYPRO	12	0.09	1.08	5600	12.4	0.112	26.4	18	6	CE		
50 X 50 X 10	AD0512HX-G90	HYPRO	12	0.08	0.96	3800	9.8	0.082	28.6	24	0	UL,CUL,CE		
50 X 50 X 10	AD0512LB-G70	BALL	12	0.06	0.72	3900	9.4	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0512LB-G72	BALL	12	0.09	1.08	3700	9.0	0.060	20.0	18	2	UL,CUL,TUV,CE		
50 X 50 X 10	AD0512LB-G73	BALL	12	0.06	0.72	3900	9.4	0.067	20.0	18	3	CE		
50 X 50 X 10	AD0512MB-G70(S)	Bor1B1S	12	0.07	0.84	4600	10.5	0.100	24.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0512MB-G73	BALL	12	0.10	1.20	4300	10.5	0.100	24.0	18	3	CE		
50 X 50 X 10	AD0512MB-G90(S)	Bor1B1S	12	0.07	0.84	3300	8.5	0.068	24.9	24	0	UL,CUL,CE		
50 X 50 X 10	AD0512MB-G96(S)	1B & 1S	12	0.07	0.84	3300	8.5	0.068	24.9	24	6	CE		
50 X 50 X 10	AD0512HB-G70(S)	Bor1B1S	12	0.09	1.08	5200	11.9	0.130	28.0	18	0	UL,CUL,TUV,CE		
50 X 50 X 10	AD0512HB-G72	BALL	12	0.11	1.32	5000	11.2	0.130	26.0	18	2	CE		
50 X 50 X 10	AD0512HB-G73(S)	1B & 1S	12	0.09	1.08	5200	11.9	0.130	28.0	18	3	CE		
50 X 50 X 10	AD0512HB-G76	BALL	12	0.09	1.08	5000	11.2	0.130	26.0	18	6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0512HB-G90(S)	Bor1B1S	12	0.08	0.96	3800	9.8	0.082	28.6	24	0	UL,CUL,CE		
50 X 50 X 10	AD0512LS-G70	S	12	0.06	0.72	3700	9.0	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0512MS-G70	S	12	0.07	0.84	4600	10.5	0.100	24.0	18	0,6	UL,CUL,TUV,CE		

NOTE B=Ball S=Sleeve X= Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

ADDA USA

DC FAN SPECIFICATIONS

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
50 X 50 X 10	AD0512MS-G90	S	12	0.08	0.96	3300	8.5	0.068	24.9	24	0,6	UL,CUL,CE		
50 X 50 X 10	AD0512HS-G70	S	12	0.09	1.08	5200	11.9	0.130	28.0	18	0	CE		
50 X 50 X 10	AD0512HS-G70(T)	S	12	0.09	1.08	5000	11.2	0.130	26.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0512HS-G70(U)	S	12	0.09	1.08	5600	12.4	0.112	26.4	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0512HS-G90	S	12	0.08	0.96	3800	9.8	0.082	28.6	24	0	UL,CUL,CE		
50 X 50 X 10	AD0512HS-G96	S	12	0.08	0.96	3800	9.8	0.082	28.6	24	6	CE		
50 X 50 X 10	AD0524LX-G70	HYPRO	24	0.07	1.68	3700	9.0	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0524MX-G70	HYPRO	24	0.08	1.92	4300	10.5	0.100	24.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0524HX-G70	HYPRO	24	0.09	2.16	5000	11.2	0.130	26.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0524LB-G70	BALL	24	0.07	1.68	3700	9.0	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0524LB-G70(S)	1B & 1S	24	0.07	1.68	3900	9.4	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0524MB-G70(S)	Bor1B1S	24	0.10	2.40	4300	10.5	0.100	24.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0524MB-G90	BALL	24	0.06	1.44	3300	8.3	1.650	27.5	50	0	CE		
50 X 50 X 10	AD0524HB-G70	BALL	24	0.11	2.64	5000	11.2	0.130	26.0	18	0,6	CE		
50 X 50 X 10	AD0524HB-G70(S)	1B & 1S	24	0.09	2.16	5200	11.8	0.130	27.0	18	0,6	CE		
50 X 50 X 10	AD0524HB-G90	BALL	24	0.09	2.16	3800	9.8	0.082	28.6	50	0	CE		
50 X 50 X 10	AD0524LS-G70	S	24	0.07	1.68	3700	9.0	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0524MS-G70	S	24	0.08	1.92	4300	10.5	0.100	24.0	18	0	UL,CUL,TUV,CE		
50 X 50 X 10	AD0524HS-G70	S	24	0.09	2.16	5000	11.2	0.130	26.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 15	AD0505HX-D71	HYPRO	5	0.26	1.30	4600	12.0	0.166	28.7	36	1	UL,CUL,TUV,CE	480	46.20
52 X 52 X 15	AD0505MB-D71	BALL	5	0.16	0.80	3700	9.7	0.106	22.6	55	1	CUL,UL,TUV,CE	480	46.20
52 X 52 X 15	AD0505HB-D70	BALL	5	0.20	1.00	4600	12.0	0.166	28.7	36	0	CUL,UL,TUV,CE	480	46.20
52 X 52 X 15	AD0505HB-D71	BALL	5	0.26	1.30	4600	12.0	0.166	28.7	36	1	CUL,UL,TUV,CE	480	46.20
52 X 52 X 15	AD0505MS-D71	S	5	0.16	0.80	3700	9.7	0.106	22.6	36	1	CUL,UL,TUV,CE	480	46.20
52 X 52 X 15	AD0505HS-D70	S	5	0.20	1.00	4600	12.0	0.166	28.7	55	0	CUL,UL,TUV,CE	480	46.20
52 X 52 X 15	AD0505HS-D71	S	5	0.26	1.30	4600	12.0	0.166	28.7	36	1	CUL,UL,TUV,CE	480	46.20
52 X 52 X 15	AD0512MX-D70	HYPRO	12	0.09	1.08	3700	9.7	0.106	22.6	55	0	UL,CUL,CE	480	46.20
52 X 52 X 15	AD0512MX-D71	HYPRO	12	0.09	1.08	3700	9.7	0.106	22.6	36	1	UL,CUL,TUV,CE	480	46.20
52 X 52 X 15	AD0512MX-D72	HYPRO	12	0.09	1.08	3700	9.7	0.106	22.6	36	2	CE+	480	46.20
52 X 52 X 15	AD0512HX-D71	HYPRO	12	0.10	1.20	4600	12.0	0.166	28.7	36	1	UL,CUL,TUV,CE	480	46.20
52 X 52 X 15	AD0512HX-D76	HYPRO	12	0.10	1.20	4600	12.0	0.166	28.7	36	6	CE	480	46.20
52 X 52 X 15	AD0512LB-D70	BALL	12	0.06	0.72	2800	6.3	0.059	14.4	55	0	CE	480	46.20
52 X 52 X 15	AD0512MB-D70	BALL	12	0.09	1.08	3700	9.7	0.106	22.6	55	0,6	UL,CUL,CE	480	46.20
52 X 52 X 15	AD0512MB-D71(S)	Bor1B1S	12	0.09	1.08	3700	9.7	0.106	22.6	36	1	UL,CUL,TUV,CE	480	46.20
52 X 52 X 15	AD0512MB-D72	BALL	12	0.09	1.08	3700	9.7	0.106	22.6	36	2,3	CE	480	46.20
52 X 52 X 15	AD0512HB-D70	BALL	12	0.10	1.20	4600	12.0	0.166	28.7	55	0	UL,CUL,CE	480	46.20
52 X 52 X 15	AD0512HB-D71	Bor1B1S	12	0.10	1.20	4600	12.0	0.166	28.7	36	1	UL,CUL,TUV,CE	480	46.20
52 X 52 X 15	AD0512HB-D73	Bor1B1S	12	0.10	1.20	4600	12.0	0.166	28.7	36	3,6	CE	480	46.20
52 X 52 X 15	AD0512UB-D71	BALL	12	0.11	1.32	5300	13.0	0.200	35.0	36	1	CE	480	46.20
52 X 52 X 15	AD0512UB-D72	BALL	12	0.11	1.32	5300	12.5	0.200	33.3	36	2	CE	480	46.20
52 X 52 X 15	AD0512MS-D70	S	12	0.09	1.08	3700	9.7	0.106	22.6	55	0	UL,CUL,CE	480	46.20
52 X 52 X 15	AD0512MS-D71	S	12	0.09	1.08	3700	9.7	0.106	22.6	36	1	UL,CUL,TUV,CE	480	46.20
52 X 52 X 15	AD0512HS-D70	S	12	0.10	1.20	4600	12.0	0.166	28.7	55	0	UL,CUL,CE	480	46.20

NOTE B=Ball S=Sleeve X= Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

ADDA USA

DC FAN SPECIFICATIONS

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
52 X 52 X 15	AD0512HS-D71	S	12	0.10	1.20	4600	12.0	0.166	28.7	36	1	UL,CUL,TUV,CE	480	46.20
52 X 52 X 15	AD0512HS-D76	S	12	0.10	1.20	4600	12.0	0.166	28.7	36	6	CE	480	46.20
52 X 52 X 15	AD0524HX-D71	HYPRO	24	0.08	1.92	4600	12.0	0.166	28.7	36	1	CE	480	46.20
52 X 52 X 15	AD0524HB-D71	BALL	24	0.08	1.92	4600	12.0	0.166	28.7	55	1	CE	480	46.20
52 X 52 X 15	AD0524HS-D71	S	24	0.08	1.92	4600	12.0	0.166	28.7	36	1	CE	480	46.20
60 X 60 X 10	AD0605LX-G90	HYPRO	5	0.15	0.75	3000	11.9	0.060	23.1	30	0	UL,CUL,CE	480	35.50
60 X 60 X 10	AD0605LX-G70	HYPRO	5	0.13	0.65	3500	10.0	0.060	23.0	30	0	CE	480	35.50
60 X 60 X 10	AD0605MX-G70	HYPRO	5	0.15	0.75	4200	12.0	0.090	28.0	23	0	TUV,CE	480	35.50
60 X 60 X 10	AD0605LB-G70	BALL	5	0.13	0.65	3500	10.0	0.060	23.0	30	0	CE	480	35.50
60 X 60 X 10	AD0605MB-G70	BALL	5	0.15	0.75	4200	12.0	0.090	28.0	23	0	TUV,CE	480	35.50
60 X 60 X 10	AD0605HB-G90	BALL	5	0.27	1.35	4200	16.6	0.115	32.8	30	0	UL,CUL,CE	480	35.50
60 X 60 X 10	AD0605LS-G70	S	5	0.13	0.65	3500	10.0	0.060	23.0	23	0	TUV,CE	480	35.50
60 X 60 X 10	AD0605LS-G90	S	5	0.14	0.70	3000	11.9	0.060	23.1	30	0	UL,CUL,CE	480	35.50
60 X 60 X 10	AD0605MS-G70	S	5	0.15	0.75	4200	12.0	0.090	28.0	23	0	TUV,CE	480	35.50
60 X 60 X 10	AD0605HS-G90	S	5	0.27	1.35	4200	16.6	0.115	32.8	30	0	UL,CUL,TUV,CE	480	35.50
60 X 60 X 10	AD0612LX-G70	HYPRO	12	0.11	1.32	3500	11.7	0.050	23.0	30	0	TUV,CE	480	35.50
60 X 60 X 10	AD0612LX-G76	HYPRO	12	0.11	1.32	3500	11.7	0.050	23.0	30	6	CE	480	35.50
60 X 60 X 10	AD0612MX-G70	HYPRO	12	0.13	1.56	4200	12.0	0.090	28.0	23	0,6	TUV,CE	480	35.50
60 X 60 X 10	AD0612MX-G90	HYPRO	12	0.12	1.44	3600	14.1	0.086	28.5	30	0,6	UL,CUL,CE	480	35.50
60 X 60 X 10	AD0612MX-G96	HYPRO	12	0.12	1.44	3600	14.1	0.086	28.5	30	6	CE	480	35.50
60 X 60 X 10	AD0612HX-G70	HYPRO	12	0.15	1.80	4900	14.5	0.108	32.0	23	0,6	TUV,CE	480	35.50
60 X 60 X 10	AD0612HX-G90	HYPRO	12	0.14	1.68	4200	16.6	0.115	32.8	30	0	UL,CUL,TUV,CE	480	35.50
60 X 60 X 10	AD0612LB-G70(S)	Bor1B1S	12	0.11	1.32	3500	11.7	0.050	23.0	30	0,6	TUV,CE	480	35.50
60 X 60 X 10	AD0612LB-G90	BALL	12	0.11	1.32	3000	11.9	0.060	23.1	30	0	UL,CUL,CE	480	35.50
60 X 60 X 10	AD0612LB-G96	BALL	12	0.11	1.32	3000	11.9	0.060	23.1	30	6	TUV,CE	480	35.50
60 X 60 X 10	AD0612MB-G70(S)	Bor1B1S	12	0.13	1.56	4200	12.0	0.090	28.0	23	0,6	TUV,CE	480	35.50
60 X 60 X 10	AD0612MB-G90(S)	Bor1B1S	12	0.12	1.44	3600	14.1	0.086	28.5	30	0,6	UL,CUL,TUV,CE	480	35.50
60 X 60 X 10	AD0612MB-GA6	BALL	12	0.19	2.28	4000	17.3	0.127	31.7	30	6	UL,CUL,TUV,CE	480	35.50
60 X 60 X 10	AD0612HB-G70(S)	Bor1B1S	12	0.15	1.80	4900	14.5	0.108	32.0	23	0,6	TUV,CE	480	35.50
60 X 60 X 10	AD0612HB-G90(S)	Bor1B1S	12	0.14	1.68	4200	16.6	0.115	32.8	30	0	UL,CUL,TUV,CE	480	35.50
60 X 60 X 10	AD0612HB-G96(S)	1B & 1S	12	0.14	1.68	4200	16.6	0.115	32.8	30	6	CE	480	35.50
60 X 60 X 10	AD0612HB-GA6(S)	1B & 1S	12	0.25	3.00	4600	21.0	0.165	35.8	30	6	UL,CUL,TUV,CE	480	35.50
60 X 60 X 10	AD0612LS-G70	S	12	0.11	1.32	3500	11.7	0.050	23.0	23	0	TUV,CE	480	35.50
60 X 60 X 10	AD0612LS-G90	S	12	0.11	1.32	300	11.9	0.060	23.1	30	0	UL,CUL,CE	480	35.50
60 X 60 X 10	AD0612LS-G96	S	12	0.11	1.32	300	11.9	0.060	23.1	30	6	UL,CUL,TUV,CE	480	35.50
60 X 60 X 10	AD0612MS-G70	S	12	0.13	1.56	4200	12.0	0.090	28.0	23	0,6	TUV,CE	480	35.50
60 X 60 X 10	AD0612HS-G90	S	12	0.15	1.80	4900	14.5	0.108	32.0	23	0	TUV,CE	480	35.50
60 X 60 X 10	AD0612HS-G96	S	12	0.15	1.80	4900	14.5	0.108	32.0	23	6	UL,CUL,TUV,CE	480	35.50
60 X 60 X 10	AD0612HS-G90	S	12	0.14	1.68	4200	16.6	0.115	32.8	30	0	UL,CUL,CE	480	35.50
60 X 60 X 10	AD0612HS-G96	S	12	0.14	1.68	4200	16.6	0.115	32.8	30	6	CE	480	35.50
60 X 60 X 15	AD0605LB-D70GL	BALL	5	0.20	1.00	3500	12.0	0.010	27.2	38	0,1	CE	300	25.70
60 X 60 X 15	AD0605MB-D71GL	BALL	5	0.25	1.25	3900	14.2	0.118	28.8	38	1,2,3	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0605HB-D70GL	BALL	5	0.25	1.25	4500	15.7	0.163	33.2	38	0	CE	300	25.70

NOTE B=Ball S=Sleeve X= Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

ADDA USA **DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
60 X 60 X 15	AD0605HB-D71GL	BALL	5	0.37	1.85	4500	16.6	0.152	32.4	38	1,2	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0605HB-D73GL	BALL	5	0.37	1.85	4500	16.6	0.152	32.4	38	3	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0605MS-D71GL	S	5	0.25	1.25	3900	14.2	0.118	28.8	38	1	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0605HS-D70GL	S	5	0.25	1.25	4500	15.7	0.163	33.2	38	0	CE	300	25.70
60 X 60 X 15	AD0605HS-D71GL	S	5	0.37	1.85	4500	16.6	0.152	32.4	38	1	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0612DX-D70GL	HYPRO	12	0.07	0.84	3100	12.2	0.086	24.9	38	0,6	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0612LX-D70GL	HYPRO	12	0.09	1.08	3500	12.0	0.010	27.2	38	0	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0612LX-D76GL	HYPRO	12	0.09	1.08	3500	12.0	0.010	27.2	38	6	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0612MX-D70GL	HYPRO	12	0.11	1.32	3900	14.2	0.118	28.8	38	0,1,2,3	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0612MX-D76GL	B,S,or X	12	0.11	1.32	3900	14.2	0.118	28.8	38	6	CE	300	25.70
60 X 60 X 15	AD0612HX-D70GL	HYPRO	12	0.13	1.56	4500	16.6	0.152	32.4	38	0,1,6	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0612HX-D72GL	HYPRO	12	0.13	1.56	4500	16.6	0.152	32.4	38	2,3	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0612DB-D70GL	BALL	12	0.07	0.84	3100	12.2	0.086	24.9	38	0,2	CE	300	25.70
60 X 60 X 15	AD0612DB-D70(T)	BALL	12	0.07	0.84	3100	10.7	0.086	23.8	38	0,6	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0612LB-D70GL	BALL	12	0.09	1.08	3500	12.0	0.010	27.2	38	0,1	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0612LB-D76GL	BALL	12	0.09	1.08	3500	12.0	0.010	27.2	38	6	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0612MB-D70GL	BALL	12	0.11	1.32	3900	14.2	0.118	28.8	38	0,1,3	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0612MB-D76GL	BALL	12	0.11	1.32	3900	14.2	0.118	28.8	38	6	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0612HB-D70GL	BALL	12	0.13	1.56	4500	16.6	0.152	32.4	38	0,1,2,3,6	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0612UB-D71GL	BALL	12	0.16	1.92	5100	18.0	0.176	39.3	38	1,2,6	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0612UB-D73GL	BALL	12	0.16	1.92	5100	18.0	0.176	39.3	38	3	CE	300	25.70
60 X 60 X 15	AD0612UB-D96	BALL	12	0.31	3.72	6000	28.5	0.231	40.4	38	6	CE	300	25.70
60 X 60 X 15	AD0612LS-D70GL	S	12	0.09	1.08	3500	12.0	0.010	27.2	38	0,1	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0612MS-D70GL	S	12	0.11	1.32	3900	14.2	0.118	28.8	38	0,1,6	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0612MS-D72GL	S	12	0.11	1.32	3900	14.2	0.118	28.8	38	2	CE	300	25.70
60 X 60 X 15	AD0612HS-D70GL	S	12	0.13	1.56	4500	16.6	0.152	32.4	38	0,1,6	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0612HS-D73GL	S	12	0.13	1.56	4500	16.6	0.152	32.4	38	3	CE	300	25.70
60 X 60 X 15	AD0624LX-D70GL	HYPRO	24	0.05	1.20	3500	12.0	0.010	27.2	38	0	CE	300	25.70
60 X 60 X 15	AD0624MX-D71GL	HYPRO	24	0.07	1.68	3900	15.0	0.138	30.7	38	1	CE	300	25.70
60 X 60 X 15	AD0624HX-D71GL	HYPRO	24	0.09	2.16	4500	17.0	0.173	33.3	38	1	TUV,CE	300	25.70
60 X 60 X 15	AD0624MB-D70GL	BALL	24	0.07	1.68	3900	15.0	0.138	30.7	38	0	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0624MB-D71GL	BALL	24	0.07	1.68	3900	15.0	0.138	30.7	38	1	CE	300	25.70
60 X 60 X 15	AD0624MB-D72GL	BALL	24	0.07	1.68	3900	15.0	0.138	30.7	38	2	TUV,CE	300	25.70
60 X 60 X 15	AD0624HB-D70GL	BALL	24	0.09	2.16	4500	17.0	0.173	33.3	38	0,6	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0624HB-D71GL	BALL	24	0.09	2.16	4500	17.0	0.173	33.3	38	1,2	TUV,CE	300	25.70
60 X 60 X 15	AD0624HB-D73GL	BALL	24	0.09	2.16	4500	17.0	0.173	33.3	38	3	CE	300	25.70
60 X 60 X 15	AD0624LS-D70GL	S	24	0.05	1.20	3500	13.0	0.110	27.2	38	0	CE	300	25.70
60 X 60 X 15	AD0624MS-D70GL	S	24	0.07	1.68	3900	15.0	0.138	30.7	38	0	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0624MS-D71GL	S	24	0.07	1.68	3900	15.0	0.138	30.7	38	1	TUV,CE	300	25.70
60 X 60 X 15	AD0624HS-D70GL	S	24	0.09	2.16	4500	17.0	0.173	33.3	38	0	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0624HS-D71GL	S	24	0.09	2.16	4500	17.0	0.173	33.3	38	1	TUV,CE	300	25.70
60 X 60 X 20	AD0605HX-C70GL	HYPRO	5	0.25	1.25	4500	16.3	0.156	29.8	49	0	CE	300	40.00
60 X 60 X 20	AD0605MB-C70GL	BALL	5	0.24	1.20	3900	14.5	0.111	25.7	49	0	CE	300	40.00

NOTE B=Ball S=Sleeve X= Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

ADDA USA

DC FAN SPECIFICATIONS

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
60 X 60 X 20	AD0605HB-C70GL	BALL	5	0.30	1.50	4500	16.4	0.139	29.7	49	0	TUV,CE	300	40.00
60 X 60 X 20	AD0605HB-C72GL	BALL	5	0.30	1.50	4500	16.4	0.139	29.7	49	2	CE	300	40.00
60 X 60 X 20	AD0605HS-C70GL	HYPRO	5	0.30	1.50	4500	16.4	0.139	29.7	49	0	CE	300	40.00
60 X 60 X 20	AD0612DX-C76GL	HYPRO	12	0.07	0.84	3000	10.7	0.054	18.4	49	6	CE	300	40.00
60 X 60 X 20	AD0612LX-C70GL	HYPRO	12	0.08	0.96	3500	13.3	0.096	21.6	49	0,6	UL,CSA,CE	300	40.00
60 X 60 X 20	AD0612MX-C70GL	HYPRO	12	0.13	1.56	3900	14.5	0.111	25.7	49	0	UL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612MX-C72GL	HYPRO	12	0.13	1.56	3900	14.5	0.111	25.7	49	2,3,6	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0612HX-C70GL	HYPRO	12	0.16	1.92	4500	16.4	0.139	29.7	49	0	UL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612HX-C72GL	HYPRO	12	0.16	1.92	4500	16.4	0.139	29.7	49	2	CE	300	40.00
60 X 60 X 20	AD0612HX-C73GL	HYPRO	12	0.16	1.92	4500	16.4	0.139	29.7	49	3,6	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0612DB-C76GL	BALL	12	0.07	0.84	3000	10.7	0.054	18.4	49	6	CE	300	40.00
60 X 60 X 20	AD0612LB-C70GL	BALL	12	0.08	0.96	3500	13.3	0.096	21.6	49	0,1	UL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612LB-C73GL	BALL	12	0.08	0.96	3500	13.3	0.096	21.6	49	3	CE	300	40.00
60 X 60 X 20	AD0612LB-C76GL	BALL	12	0.08	0.96	3500	13.3	0.096	21.6	49	6	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0612MB-C70GL	BALL	12	0.13	1.56	3900	14.5	0.111	25.7	49	0,3	UL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612MB-C72GL	BALL	12	0.13	1.56	3900	14.5	0.111	25.7	49	2,6	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0612HB-C70GL	BALL	12	0.16	1.92	4600	16.4	0.139	29.7	49	0,1,6	UL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612HB-C72GL	BALL	12	0.16	1.92	4600	16.4	0.139	29.7	49	2,3	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0612UB-C71GL	BALL	12	0.17	2.04	5100	18.7	0.160	34.6	49	1	CE	300	40.00
60 X 60 X 20	AD0612LS-C70GL	S	12	0.08	0.96	3500	13.3	0.096	21.6	49	0	UL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612LS-C71GL	S	12	0.08	0.96	3500	13.3	0.096	21.6	49	1	UL,CUL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612LS-C76GL	S	12	0.08	0.96	3500	13.3	0.096	21.6	49	6	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0612MS-C70GL	S	12	0.13	1.56	3900	14.5	0.111	25.7	49	0,1,6	UL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612MS-C72GL	S	12	0.13	1.56	3900	14.5	0.111	25.7	49	2,3	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0612HS-C70GL	BALL	12	0.16	1.92	4500	16.4	0.139	29.7	49	0,1,6	UL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612HS-C72GL	BALL	12	0.16	1.92	4500	16.4	0.139	29.7	49	2,3	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0624MX-C70GL	HYPRO	24	0.08	1.92	3900	14.5	0.111	25.7	49	0	UL,CUL,TUV,CE	300	40.00
60 X 60 X 20	AD0624HX-C70GL	HYPRO	24	0.09	2.16	4500	16.4	0.139	29.7	49	0	UL,CUL,TUV,CE	300	40.00
60 X 60 X 20	AD0624MB-C70GL	BALL	24	0.08	1.92	3900	14.5	0.111	25.7	49	0	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0624HB-C70GL	BALL	24	0.09	2.16	4500	16.4	0.139	29.7	49	0,1	UL,CUL,TUV,CE	300	40.00
60 X 60 X 20	AD0624HB-C70(T)	BALL	24	0.09	2.16	4500	16.4	0.139	29.7	49	0,6	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0624MS-C70GL	S	24	0.08	1.92	3900	14.5	0.111	25.7	49	0	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0624HS-C70GL	S	24	0.09	2.16	4500	16.4	0.139	29.7	49	0	UL,CUL,TUV,CE	300	40.00
60 X 60 X 25	AD0605MX-A70GL	HYPRO	5	0.32	1.60	3500	18.0	0.118	24.0	68	0	UL,CUL,CE	300	44.00
60 X 60 X 25	AD0605MB-A70GL	BALL	5	0.32	1.60	3500	18.0	0.188	24.0	68	0	UL,TUV,CE	300	40.00
60 X 60 X 25	AD0605HB-A70GL	BALL	5	0.45	2.25	4500	23.2	0.188	32.3	68	0,2	TUV,CE	300	44.00
60 X 60 X 25	AD0605HB-A73GL	BALL	5	0.45	2.25	4500	23.2	0.188	32.3	68	3	CE	300	44.00
60 X 60 X 25	AD0605MS-A70GL	S	5	0.32	1.60	3500	18.0	0.188	24.0	68	0	UL,CUL,CE	300	40.00
60 X 60 X 25	AD0605HS-A71GL	S	5	0.60	3.00	4500	23.2	0.188	32.3	68	1	CE	300	40.00
60 X 60 X 25	AD0612LX-A70GL	HYPRO	12	0.08	0.96	2500	13.2	0.063	16.1	68	0	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612LX-A72GL	HYPRO	12	0.08	0.96	2500	13.2	0.063	16.1	68	2,3	UL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612MX-A70GL	HYPRO	12	0.14	1.68	3500	18.0	0.188	24.0	68	0,6	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612MX-A73GL	HYPRO	12	0.14	1.68	3500	18.0	0.188	24.0	68	3	UL,CUL,TUV,CE	300	44.00

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

ADDA USA

DC FAN SPECIFICATIONS

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
60 X 60 X 25	AD0612HX-A70GL	HYPRO	12	0.23	2.76	4500	23.2	0.188	32.3	68	0,1,2	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612HX-A73GL	HYPRO	12	0.23	2.76	4500	23.2	0.188	32.3	68	3,6	UL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612UX-A70GL	HYPRO	12	0.25	3.00	5000	28.3	0.250	37.0	68	0	CE	300	44.00
60 X 60 X 25	AD0612UX-A71GL	HYPRO	12	0.27	3.24	5300	28.3	0.250	37.0	68	1	UL,CUL,CE	300	44.00
60 X 60 X 25	AD0612UX-A72GL	HYPRO	12	0.27	3.24	5300	28.3	0.250	37.0	68	2,3	CE	300	44.00
60 X 60 X 25	AD0612LB-A70GL	BALL	12	0.08	0.96	2500	13.2	0.063	16.1	68	0,1	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612LB-A70(T)	BALL	12	0.08	0.96	2300	10.7	0.041	14.5	68	0,6	UL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612MB-A70GL	BALL	12	0.14	1.68	3500	18.0	0.118	24.0	68	0	UL,CUL,TUV,CE	300	44.00
60 X 60 X 25	AD0612MB-A71GL	BALL	12	0.14	1.68	3500	18.0	0.118	24.0	68	1	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612MB-A72GL	BALL	12	0.14	1.68	3500	18.0	0.118	24.0	68	2,3	UL,CUL,TUV,CE	300	44.00
60 X 60 X 25	AD0612MB-A76GL	BALL	12	0.14	1.68	3500	18.0	0.118	24.0	68	6	CE	300	44.00
60 X 60 X 25	AD0612HB-A70GL	BALL	12	0.23	2.76	4500	23.2	0.188	32.3	68	0,1	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612HB-A72GL	BALL	12	0.23	2.76	4500	23.2	0.188	32.3	68	2,3,6	UL,CUL,TUV,CE	300	44.00
60 X 60 X 25	AD0612UB-A70GL	BALL	12	0.25	3.00	5000	28.3	0.250	37.0	68	0	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612UB-A71GL	BALL	12	0.25	3.00	5000	28.3	0.250	37.0	68	1	UL,CUL,TUV,CE	300	44.00
60 X 60 X 25	AD0612UB-A72GL	BALL	12	0.25	3.00	5000	28.3	0.250	37.0	68	2,3	UL,CUL,CE	300	44.00
60 X 60 X 25	AD0612UB-A76GL	BALL	12	0.25	3.00	5000	28.3	0.250	37.0	68	6	CE	300	44.00
60 X 60 X 25	AD0612XB-A71GL	BALL	12	0.38	4.56	6100	31.4	0.320	42.9	68	1,2,3	CE	300	44.00
60 X 60 X 25	AD0612XB-A72/UP	BALL	12	0.65	7.80	7400	38.1	0.500	47.8	68	2	CE	300	44.00
60 X 60 X 25	AD0612LS-A70GL	S	12	0.08	0.96	2500	13.2	0.063	16.1	68	0,1	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612LS-A73GL	S	12	0.08	0.96	2500	13.2	0.063	16.1	68	3	UL,CUL,TUV,CE	300	44.00
60 X 60 X 25	AD0612LS-A76GL	S	12	0.08	0.96	2500	13.2	0.063	16.1	68	6	CE	300	44.00
60 X 60 X 25	AD0612MS-A70GL	S	12	0.14	1.68	3500	18.0	0.118	24.0	68	0	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612MS-A76GL	S	12	0.14	1.68	3500	18.0	0.118	24.0	68	6	TUV,CE	300	44.00
60 X 60 X 25	AD0612HS-A70GL	S	12	0.23	2.76	4500	23.2	0.188	32.3	68	0,1	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612HS-A72GL	S	12	0.23	2.76	4500	23.2	0.188	32.3	68	2,6	CE	300	44.00
60 X 60 X 25	AD0612HS-A73GL	S	12	0.23	2.76	4500	23.2	0.188	32.3	68	3	UL,CE	300	44.00
60 X 60 X 25	AD0612US-A70GL	S	12	0.25	3.00	5000	28.3	0.250	37.0	68	0,6	CE	300	44.00
60 X 60 X 25	AD0612US-A71GL	S	12	0.27	3.24	5300	28.3	0.250	37.0	68	1	TUV,CE	300	44.00
60 X 60 X 25	AD0612US-A73GL	S	12	0.27	3.24	5300	28.3	0.250	37.0	68	3	CE	300	44.00
60 X 60 X 25	AD0624MX-A70GL	HYPRO	24	0.08	1.92	3500	18.0	0.118	24.0	68	0	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0624MX-A76GL	HYPRO	24	0.08	1.92	3500	18.0	0.118	24.0	68	6	CE	300	44.00
60 X 60 X 25	AD0624HX-A70GL	HYPRO	24	0.15	3.60	4500	23.2	0.188	32.3	68	0,1	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0624HX-A72GL	HYPRO	24	0.15	3.60	4500	23.2	0.188	32.3	68	2	CE	300	44.00
60 X 60 X 25	AD0624UX-A71GL	HYPRO	24	0.16	3.84	5000	28.3	0.250	37.0	68	1,2	CE	300	44.00
60 X 60 X 25	AD0624LB-A70GL	BALL	24	0.05	1.20	2500	16.0	0.079	16.1	68	0	UL,CUL,CE	300	44.00
60 X 60 X 25	AD0624MB-A70GL	BALL	24	0.08	1.92	3500	18.0	0.118	24.0	68	0,1	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0624HB-A70GL	BALL	24	0.15	3.60	4500	23.2	0.188	32.3	68	0	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0624HB-A71GL	BALL	24	0.15	3.60	4500	23.2	0.188	32.3	68	1	UL,CSA,TUV,CE	300	44.00
60 X 60 X 25	AD0624HB-A72GL	BALL	24	0.15	3.60	4500	23.2	0.188	32.3	68	2,3	UL,CUL,CE	300	44.00
60 X 60 X 25	AD0624HB-A76GL	BALL	24	0.15	3.60	4500	23.2	0.188	32.3	68	6	CE	300	44.00
60 X 60 X 25	AD0624UB-A70GL	BALL	24	0.16	3.84	5000	26.5	0.204	38.1	68	0,1,2,3	CE	300	44.00
60 X 60 X 25	AD0624LS-A70GL	S	24	0.05	1.20	2500	16.0	0.079	16.1	68	0	UL,CUL,TUV,CSA,CE	300	44.00

NOTE B=Ball S=Sleeve X= Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

ADDA USA
DC FAN SPECIFICATIONS

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
60 X 60 X 25	AD0624MS-A70GL	S	24	0.08	1.92	3500	18.0	0.118	24.0	68	0,1	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0624MS-A72GL	S	24	0.08	1.92	3500	18.0	0.118	24.0	68	2	CE	300	44.00
60 X 60 X 25	AD0624HS-A70GL	S	24	0.15	3.60	4500	23.2	0.188	32.3	68	0,1	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0624HS-A72GL	S	24	0.15	3.60	4500	23.2	0.188	32.3	68	2	CE	300	44.00
60 X 60 X 25	AD0624HS-A73GL	S	24	0.15	3.60	4500	23.2	0.188	32.3	68	3	UL,CE	300	44.00
60 X 60 X 25	AD0624US-A71GL	S	24	0.16	3.84	5000	28.3	0.250	37.0	68	1	TUV,CE	300	44.00
NOTE B=Ball S=Sleeve X= Hypro AT= Terminals AW= Wires												ALL RIGHTS RESERVED		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ADDA:

[AD0624HB-A70GL](#) [AD0612HB-G76\(TS\)](#) [AD0605HB-D73GL](#) [AD0605HB-D71GL](#) [AD0605MB-G70](#) [AD0605MB-D71GL](#) [AD0612LB-A73GL](#) [AD0605LB-A72GL](#) [AD0612UB-A73GL-3P](#) [AD0612HB-D76GL](#) [AD0605MX-D71GL](#) [AD0624HX-A70GL](#) [AD0624HX-C70GL](#) [AD0605MB-A70GL](#) [AD0605HB-A70GL](#) [AD0605HB-D72GL](#) [AD0605MS-G70](#) [AD0612MB-D71GL](#) [AD0624HB-D71GL](#) [AD0612HX-D71GL](#) [AD0612UBA70GL](#) [AD0612HX-G76\(TS\)](#) [AD0612MS-C71GL](#) [AD0612UB-D72GL](#) [AD0612HB-D71GL-12"](#) [AD0624HB-A76GL](#) [AD0605MB-G90](#) [AD0624HB-A71GL](#) [AD0624HS-D71GL](#) [AD0624MS-A70GL\(T\)](#) [AD0612HB-G70](#) [AD0612XB-A72GL\(P\)](#) [AD0612HX-G70](#) [AD0612MB-A71GL](#) [AD0612XB-A71GL](#) [AD0612MS-A70GL](#) [AD0612HB-GA6\(GL\)-LF](#) [AD0612LB-D72GL-LF](#) [AD0624MS-A70GLT30-LF](#) [AD0612HB-A27GL-LF](#) [AD0624HB-A70GL\(T\)-LF](#) [AD0612HB-A71GL-LF](#) [AD0612MB-G70-LF](#) [AD0605HB-G70](#) [AD0612HB-D71GL-12"-LF](#) [AD0612HX-D71GL-LF](#) [AD0612MX-A70GL\(T\)-LF](#) [AD0612HX-A71GL-LF](#) [AD0624LB-A71GL-29"LF](#) [AD0624HB-C71GL-LF](#) [AD0612HB-D71GL-LF](#) [AD0624MB-A706L-LF](#) [AD0612HB-GA0GL-LF](#) [AD0605MX-D71GL-LF](#) [AD0605HB-A70GL\(T\)-LF](#) [AD0612UB-D70GL\(T\)-LF](#) [AD0612UB-A71GL\(P\)-LF](#) [AD0612HB-GA0-LF](#) [AD0612HB-G70-LF](#) [AD0624HS-A76GL-LF](#) [AD0612HB-D71GL](#) [AG06012HB257002\(00L5\)-LF](#) [AG06012MB257002\(00L5\)-LF](#) [AG06005LB257202\(00L5\)-LF](#) [AD06005MB-257200-LF](#) [AG06024MB257002\(00L5\)-LF](#) [AG06024HX257002\(00L5\)-LF](#) [AG06012HX257102\(00L5\)-LF](#) [AG06024LB257002\(00L5\)-LF](#) [AG06012HX257002\(00L5\)-LF](#) [AG06005LB257202\(0H5\)-LF](#) [AG06012LB257002\(00L5\)-LF](#) [AG06012MX257002\(00L5\)-LF](#) [AG06005MB257002\(00L5\)-LF](#) [AD06005MB257200-LF](#)