



Search:

Go

[Products](#)[Catalogs](#)[Search](#)[Customer Support](#)[About Cannon](#)[Home](#)

Standard D (Stamped)

PART NUMBER: DA15PK87

Where Sold	Americas, Asia Pacific, Europe
Product Group	D-Subminiature
Product Sub-Family	D-Sub Standard
Component Type	Connector
Application Type	Commercial
Cable or PC Board	Cable
Gender	Plug
Number of Signal Pins	15
Number of Size 8 contacts	0
Straight or Right Angle	Straight
Contact Plating	Gold over Nickel
Shell Plating	Tin (with Grounding Dimples)
Hardware	3,05 (.120) Through Holes
Contact Termination	Solder Cup
Shell Size	DA
Temperature Rating	-55°C to +125°C
Current Capacity	7.5 A
Contact Resistance	8 milli ohms max.
Dielectric Withstanding Voltage	1250 V AC at Sea Level
Reference Industry Specifications	Mil-PRF-24308
Insulator Material	Green Polyester UL 94V-0
Contact Material	Copper Alloy
Shell Material	Steel

[Sales Support](#)[Ask a Specialist](#)[Product Home](#)[Stock Check](#)[Sign In](#) | [Contact Us](#) | [Legal Disclaimer](#) | [Privacy Policy](#) | [Home](#)

© 2006 ITT Industries