

Cover Screws

-Hexagon Socket Head / Knurled-


Reduced
Days to Ship

GUTB can be ordered by a cost-saving box. P1924




Hexagon Socket Head RoHS

GUTB




M	A	E	B	d	D
2	3.8	2	1.5	1.5	-
2.6	4.5	2.5	2	1.8	-
3	5.5	3	2.5	2.2	7
4	7	4	3	3	10
5	8.5	5	4	3.9	12
6	10	6	5	4.5	12
8	13	8	6	6.3	14




Strength Class A2-70 equivalent
Material: 302 HQ Stainless Steel

GUTBN(With Nylon Washer)



The screw will not drop off from the cover when the cover is removed from the frame.
(The cover requires tap machining to prevent screws from falling off.)



Strength Class A2-70 equivalent
Material: 302 HQ Stainless Steel


Part Number	Type	M (Coarse)	L	GUTB	
				Unit Price	1~29 pcs. 30 pcs. or more
2	2.5	4 6 8 10 12 15		1.40	1.10
2.6	3	6 8 10 12 15			
3	3.5	2 4 6 8 10 12 15		1.30	1.00
4	4	6 8 10 12 15 20			
5	5	8 10 12 15 20		1.10	0.90
6	6	10 12 15 20 25		1.20	0.95
8	8	12 15 20 25 30		1.20	0.95
10	10	15 20 25 30 40		1.40	1.10

Part Number	Type	M (Coarse)	L	GUTBN	
				Unit Price	1~29 pcs. 30 pcs. or more
3	3.5	6 8 10 12 15		1.80	1.50
4	4	8 10 12 15 20		2.00	1.70
5	5	10 12 15 20		2.10	1.80
6	6	12 15 20 25		2.10	1.80
8	8	15 20 30		2.30	2.00
10	10	20 30 40			



Knurled RoHS

RNCB



Material: 303 Stainless Steel

Part Number	Type	M	L	A	d1	d2	E	Unit Price	
								1~29 pcs.	30 pcs. or more
3	3.5	4 6 8 10 12 15		12	2.2	6	2.5	3.30	2.50
4	4	6 8 10 12 15 20		16	3	8	3.5	3.80	2.90
5	5	8 10 12 15 20 25		20	3.9	10	4	5.50	4.30
6	6	12 15 20 25		24	4.5	12	5	6.70	5.30
8	8	15 20		30	6.3	16	6	11.70	9.00

Order Example

Part Number - L - L

GUTB5 - 6 - 12

GUTBN3 - 4 - 12

RNCB4 - 5 - 15

Days to Ship

GUTB RNCB (Section)

1 Day P87

Others

3 Days P87

Alterations

Part Number - MC

GUTB5 - MC5-LC10

6 Days Applicable to GUTB only.

Non-Returnable P88

Alteration	Code	Spec.	Price Adder
	MC	Thread length and L dimension can be specified in 1 mm increments. Ordering Code MC3-LC10 M MC LC M MC LC 2 2~6 4~15 5 3~15 8~25 2.6 2~8 6~15 6 4~18 8~30 3 2~9 4~20 8 5~24 8~40 4 3~12 6~20 LC-MC21	3.00


Cover Screws

-Button Head Cap Screws / Configurable Length-



Button Head Cap Screw RoHS

CBBT



Strength Class A2-50 equivalent
Material: 302 HQ Stainless Steel

Part Number	Type	M	L	L	A	E (Max.)	B	C (Min.)	d	Unit Price	
										1~29 pcs.	30 pcs. or more
3	3	8 10 12 15 20		4	5.5	1.6	2	1.04	2.2	3.50	2.60
4	4	10 12 15 20		5	7.5	2.2	2.5	1.3	3	3.70	2.70
5	5	12 15 20 25		6	9.5	2.7	3	1.56	3.9	3.80	2.80
6	6	12 15 20 25		8	10.5	3.3	4	2.08	4.5	3.90	2.80
8	8	12 15 20 25		10	14	4.4	5	2.6	6.3	4.30	3.00

Order Example

Part Number - L

CBBT5 - 20

Days to Ship


3 Days P87



Configurable Length Hexagon Socket Head RoHS

FGUTM FGUTS

Type	Material	Surface Treatment	Strength Class
FGUTM	4137 Alloy Steel	Electroless Nickel Plating	8.8 equivalent
FGUTS	302 HQ Stainless Steel	-	A2-70 equivalent






Configurable Length Knurled RoHS

FRNCS

Type	Material
FRNCS	303 Stainless Steel






Configurable Length Button Head Cap Screw RoHS

FCBBS

Type	Material	Strength Class
FCBBS	302 HQ Stainless Steel	A2-50 equivalent



Part Number	Type	M	1mm Increment				L	L	L	L / L Machining Conditions	Unit Price			
			FGUTM FGUTS	FRNCS	FCBBS	FGUTM FGUTS	FRNCS	FCBBS			FGUTM	FGUTS	FRNCS	FCBBS
3	3	2~18	5~16	5~20	4~20	6~20	6~20	6~20	6~20	≤L	4.20	4.30	4.90	4.50
4	4	3~18	5~16	5~25	6~20	6~20	6~20	6~30	6~30	≤L	4.00	4.10	5.80	4.60
5	5	3~23	5~20	5~25	8~25	8~25	8~25	8~30	8~30	≤L	4.10	4.20	8.10	4.70
6	6	4~28	8~20	8~30	8~30	8~25	8~25	8~35	8~35	≤L	4.10	4.20	9.00	4.80
8	8	5~38	10~20	10~45	8~40	8~25	8~25	8~50	8~50	≤L	4.30	4.40	11.90	5.00

M	A	A1	A2	E	E1	E2 (Max.)	B	B2	C (Min.)	d	d2
3	5.5	12	5.5	3	2.5	1.6	2.5	2	1.04	2.2	6
4	7	16	7.5	4	3.5	2.2	3	2.5	1.3	3	8
5	8.5	20	9.5	5	4	2.7	4	3	1.56	3.9	10
6	10	24	10.5	6	5	3.3	5	4	2.08	4.5	12
8	13	30	14	8	6	4.4	6	5	2.6	6.3	16

Order Example

Part Number - L - L

FRNCS6 - 8 - 20

Days to Ship

6 Days P88

Non-Returnable P88

Volume Discount Rate

Qty.	1~9	10~19	20~29	30~
Discount Rate	Unit Price	5%	10%	15%

For larger quantity orders "Days to Ship" may differ from published catalog term. P87