

2589-ID-10

NOTES:

1. THESE MOUNTING CLIPS ARE FOR HOLDING THE 2481 SERIES HOUSINGS TO THE MAIN PANEL TOPS OF ELECTRIC RANGES.
2. SCREW SIZE INDICATION.
3. .015/(.38) MAXIMUM CUT OFF.
4. .010/(.25) MAXIMUM MISMATCH.
5. THREAD FORM FOR A #10-32 SCREW.
6. THIS SURFACE MAY BE FORMED IN THIS DIRECTION A MAXIMUM OF 5°.

MATERIAL:

STEEL, STAINLESS, TYPE 301, .020/(.5) THICK.

DIMENSIONS SHOWN (METRIC) INCH	
UNLESS OTHERWISE SPECIFIED	
TOLERANCES ANGULAR ± .006 5°	
3 PLACE ± .010	---
2 PLACE ± .014	± 0.25
1 PLACE ---	± 0.35
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	
DRW'G. BY RHR	CHK'D. BY ESS
APP'D. BY RAS	SCALE 2: 1


FILE NAME SD2589X1	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.	DATE 11/20/92	SIZE CP
SEE SHEET 3		SD-2589-*	
MOUNTING CLIP		NO P.S.	

MFG. SH.	REV.	LTR.	REVISIONS
3	AB		
2	Z		
1	AC	X	REDRAWN & REDIM. ECN U2 I712 11/25/92 RHR

AC	OBSOLETE P/N UCR2002-0255 01/9/12 COMERC
AB2	REMOVED NOTCH UCR2000-0104 8/11/99 COMERC
AB1	REV. RADII UCR2000-0086 8/05/99 COMERC
AB	REVISED UCR 1999-0818 6/03/99 ELHAG
AA	REVISED ECN U4 0744 6/16/94 RHR
Z	REVISED ECN U4 0213 2/14/94 RHR
Y	REVISED ECN U3 0739 5/13/93 RHR



I3	I2	I1	I0	9	8	7	6	2589	4	3	2	I
----	----	----	----	---	---	---	---	------	---	---	---	---

	PART NO.	ENG. NO.	DIMENSION	
			A	
J	089-00-2006	2589-ID-10	.48±.025 (12.2±.64)	
	089-00-2022	2589-2C	.53±.025 (13.5±.64)	
	089-00-2025	2589-2H	.656±.025 (16.66±.64)	
I	089-00-2027	2589-2J-10	.562±.025 (14.27±.64)	
	089-00-2041	2589-3B	.48±.025 (12.2±.64)	
	089-00-2047	2589-6F	.375±.015 (9.53±.38)	
H	089-00-2100	2589-10C	.48±.025 (12.2±.64)	
	089-00-2101	2589-21A	.62±.025 (15.7±.64)	OBSOLETE
	089-00-2103	2589-23	.62±.025 (15.7±.64)	




FOR THE REMAINDER
OF DIMENSIONS AND
DETAILS SEE SHEET I

2589-23



FOR THE REMAINDER
OF DIMENSIONS AND
DETAILS SEE SHEET I

2589-21A OBSOLETE



				AA	SEE SHEET I	DIMENSIONS SHOWN (METRIC) INCH UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 1° 5'				▽ = 0 ▼ = 0		REVISE ONLY ON CAD SYSTEM																					
				Z	SEE SHEET I	<table><tr><th colspan="2">INCH</th><th colspan="2">METRIC</th></tr><tr><td>3 PLACE</td><td>± .010</td><td colspan="2">---</td></tr><tr><td>2 PLACE</td><td>± .014</td><td colspan="2">± 0.25</td></tr><tr><td>1 PLACE</td><td>---</td><td colspan="2">± 0.35</td></tr></table>				INCH		METRIC		3 PLACE	± .010	---		2 PLACE	± .014	± 0.25		1 PLACE	---	± 0.35		TITLE		MOUNTING CLIP					
INCH		METRIC																															
3 PLACE	± .010	---																															
2 PLACE	± .014	± 0.25																															
1 PLACE	---	± 0.35																															
AB				SEE SHEET I	X	SEE SHEET I	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				MOLEX INCORPORATED LITTLE ROCK, AR 69532 U.S.A.		SHEET NO. 3	DATE 2/24/93																			
							DRWG. NO. SD-2589-3		SEE CHART		SD-2589-3																						
LTR.				REVISIONS	LTR.	REVISIONS	APP'D. BY RAS		CHK'D. BY ESS		FILE NAME SD2589X3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.		DIV. CP	SIZE C																	